

THA-301JB Lever Handle Latch



■ Characteristic

With modified slide cap design, safety and operability have been increased. Having size of large, medium, and small, with key or without key, select one for your application.

■ Application

Distribution boards / Distribution panels / Control boards / Various types of boxes

■ Specification

Can be set on left side or right side, and the making the change can be done easily.
All keys have the same key No. Cylinder locks by 180-degree turn clockwise.
Insert or taking off the key can be done at both lock and unlock positions.
Waterproof specification using an O-ring.

■ Specification


Model No.	Net Weight (g)	Code No.	
THA-301JB-1K	474	3335	
THA-301JB-1	486	3336	
THA-301JB-2K	340	3337	
THA-301JB-2	338	3338	
THA-301JB-3K	298	3339	
THA-301JB-3	294	3340	

※No.200 key is available.

※Consult with us for color specification.

■ Parts List

No.	Part Name	Material	Finish	Quantity
1	Body	ZDC	N7 (Gray)	1
2	Receiver			1
3	Packing	CR	Black	1
4	Toothed Lock Washer	S	Zn	1
5	Set Nut	ZDC		1
6	Square Hole Washer	SPCC		1
7	Square Hole Washer			1
8	Flat Washer			1
9	Hexagon Bolt	S		1
10	Cap	ZDC	N7 (Gray)	1
11	Lock	ZDC/SUS	Zn	1
12	Key	BSP	Ni	2



■ Size List

Model No.	A	B	B1	B2	C	D1	D2	E	F	G	H	J
THA-301JB-1K	120	27	34	ϕ 60	48.5	22.5	8	35	40	ϕ 8.5	16	☐ 10
THA-301JB-1												
THA-301JB-2K												
THA-301JB-2	100	25	32	ϕ 48		14.3					15	☐
THA-301JB-3K					44.5		5	30	32	ϕ 8.0		☐ 8
THA-301JB-3	80	23	30	ϕ 46		14.8					12	