






			
art. no.	⌀	↑ [mm]	R _{th} [K/W]	art. no.	⌀	↑ [mm]	R _{th} [K/W]
FK 318 SA	without	31.8	4.8	FK 318 SA-3	TO 3	31.8	4.8
FK 254 SA	without	25.4	5.8	FK 254 SA-3	TO 3	25.4	5.8
FK 191 SA	without	19.1	6.6	FK 191 SA-3	TO 3	19.1	6.6
FK 127 SA	without	12.7	8.0	FK 127 SA-3	TO 3	12.7	8.0

material: die-cast aluminium
surface treatment: black lacquered

									
art. no.		$\updownarrow$ [mm]	R_{th} [K/W]	art. no.		$\updownarrow$ [mm]	R_{th} [K/W]		
FK 201 SA	without	25.4	6	FK 202 SA	without	12.7	8		
FK 201 SA 3	TO 3	25.4	6	FK 202 SA 3	TO 3	12.7	8		
FK 201 SA CB	CB	25.4	6	FK 202 SA CB	CB	12.7	8		

						
art. no.		$\updownarrow$ [mm]	R_{th} [K/W]			
FK 205 SA L	L	31.8	9.0			
FK 206 SA L	L	25.4	10.5			
FK 207 SA L	L	19.1	12.0			
FK 208 SA L	L	12.7	14.0			

material: aluminium
surface treatment: black anodised