

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0351890360](#)
Status: **Obsolete**
Description: 4.75mm (.187") Tab, MP-Lock™ Housing, 3 Circuits, 6.00mm (.236") Pitch, 6.65mm (.261") Pitch, UL94V-2, Natural

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR95446
UL	E29179

General

Product Family	Crimp Housings
Series	35189
Application	Power
Product Name	MP-Lock™

Physical

Breakaway	No
Circuits (maximum)	3
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	None
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.00mm (.236"), 6.65mm (.262")
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	12A
-------------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35189-003
Product Specification	PS-35189-001, RPS-35068-001
Sales Drawing	SD-35189-0360




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35189Series](#)

Mates With
Micro Switch

Use With
[35068](#) MP-Lock™ Quick Disconnect

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION