



# DUAL-IN-LINE SOCKETS

## SERIES 115...001 • VERY LOW PROFILE • OPEN FRAME



- Low profile DIP socket, sits only 3,1mm above the PCB
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 115 uses MM #0501 pins. See page 162 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



| Total number of pins             |      |       |      | Quantity per tube | ORDERING INFORMATION                 |              |
|----------------------------------|------|-------|------|-------------------|--------------------------------------|--------------|
|                                  | A    | B     | C    |                   |                                      |              |
| 10                               | 12,6 | 5,08  | 7,6  | 41                | 115-XX-210-41-001000                 |              |
| 4                                | 5,0  | 7,62  | 10,1 | 102               | 115-XX-304-41-001000                 |              |
| 6                                | 7,6  | 7,62  | 10,1 | 67                | 115-XX-306-41-001000                 |              |
| 8                                | 10,1 | 7,62  | 10,1 | 50                | 115-XX-308-41-001000                 |              |
| 10                               | 12,6 | 7,62  | 10,1 | 40                | 115-XX-310-41-001000                 |              |
| 14                               | 17,7 | 7,62  | 10,1 | 28                | 115-XX-314-41-001000                 |              |
| 16                               | 20,3 | 7,62  | 10,1 | 25                | 115-XX-316-41-001000                 |              |
| 18                               | 22,8 | 7,62  | 10,1 | 22                | 115-XX-318-41-001000                 |              |
| 20                               | 25,3 | 7,62  | 10,1 | 20                | 115-XX-320-41-001000                 |              |
| 22                               | 27,8 | 7,62  | 10,1 | 18                | 115-XX-322-41-001000                 |              |
| 24                               | 30,4 | 7,62  | 10,1 | 16                | 115-XX-324-41-001000                 |              |
| 28                               | 35,5 | 7,62  | 10,1 | 14                | 115-XX-328-41-001000                 |              |
| 20                               | 25,4 | 10,16 | 12,7 | 20                | 115-XX-420-41-001000                 |              |
| 22                               | 27,8 | 10,16 | 12,7 | 18                | 115-XX-422-41-001000                 |              |
| 24                               | 30,4 | 10,16 | 12,7 | 16                | 115-XX-424-41-001000                 |              |
| 28                               | 35,5 | 10,16 | 12,7 | 14                | 115-XX-428-41-001000                 |              |
| 32                               | 40,6 | 10,16 | 12,7 | 12                | 115-XX-432-41-001000                 |              |
| 24                               | 30,4 | 15,24 | 17,7 | 16                | 115-XX-624-41-001000                 |              |
| 28                               | 35,5 | 15,24 | 17,7 | 14                | 115-XX-628-41-001000                 |              |
| 32                               | 40,6 | 15,24 | 17,7 | 12                | 115-XX-632-41-001000                 |              |
| 36                               | 45,7 | 15,24 | 17,7 | 11                | 115-XX-636-41-001000                 |              |
| 40                               | 50,8 | 15,24 | 17,7 | 10                | 115-XX-640-41-001000                 |              |
| 42                               | 53,3 | 15,24 | 17,7 | 9                 | 115-XX-642-41-001000                 |              |
| 48                               | 60,9 | 15,24 | 17,7 | 8                 | 115-XX-648-41-001000                 |              |
| 50                               | 63,5 | 15,24 | 17,7 | 8                 | 115-XX-650-41-001000                 |              |
| 52                               | 66,0 | 15,24 | 17,7 | 7                 | 115-XX-652-41-001000                 |              |
| 50                               | 63,5 | 22,86 | 25,3 | 8                 | 115-XX-950-41-001000                 |              |
| 52                               | 66,0 | 22,86 | 25,3 | 7                 | 115-XX-952-41-001000                 |              |
| 64                               | 81,2 | 22,86 | 25,3 | 6                 | 115-XX-964-41-001000                 |              |
| <b>SPECIFY PLATING CODE XX =</b> |      |       |      |                   | <div>XX=Plating Code See Below</div> |              |
| Sleeve (Pin)                     |      |       |      |                   | 91                                   | 93           |
| Contact (Clip)                   |      |       |      |                   | 41                                   | 43           |
|                                  |      |       |      |                   | 5,08µm Sn/Pb                         | 5,08µm Sn/Pb |
|                                  |      |       |      |                   | 0,25µm Au                            | 0,76µm Au    |
|                                  |      |       |      |                   | 5,08µm Sn                            | 5,08µm Sn    |
|                                  |      |       |      |                   | 0,25µm Au                            | 0,76µm Au    |

