





Material and Finish:

- 1.Insulator Material: P.B.T,UL94V-0,Color:Black
- 2.Contact Material: Brass
- 3.Shell Material: Steel
- 4.River,Boardlock: Copper alloy
- 5.Contact Plating: 40u" Gold Plated Over Nickel
- 6.Current Rating: 3 Amps Max.
- 7.Contact Resistance: 15 mohms Max.
- 8.Insulation Resistance: 3000 Mohms Min.
- 9.Dielectric Withstanding Voltage: 1000V AC
- 10.Operation Voltage: 250 VAC Max.
- 11.Operating Temperature: -55°C to +105°C
- 12.R0 = RoHS



RECOMMENDED P.C.B LAYOUT
TOLERANCES: ±0.10



PART NO.	TITLE	A	B	C	D	E
11500320	DR-09PE-G-60-R0	16.92	25.00	30.8	8.31	11.08
	DR-15PE-G-60-R0	25.25	33.30	39.2	16.62	19.39
	DR-23PE-G-60-R0	35.90	44.30	50.3	27.70	30.47
	DR-25PE-G-60-R0	38.96	47.10	53.1	30.47	33.24
	DR-37PE-G-60-R0	55.42	63.50	69.4	47.09	49.86

UNLESS OTHERWISE SPECIFIED TOLERANCE
ANG. 0 ±0.5
0 ±0.3
0 ±0.2

SCALE: NONE UNIT: mm

DRAWN: 葉玉剛 3/24/05

CHECKED: 3/30/05

APPROVED: 3/30/05

SIZE A4 REV. A0

APPLICATION NO.: ECN-0503018

DRAWN NAME: DR-XXPE-G-60-R0

ECN-0503018

03/24/05

DESCRIPTION

DATE

REV.

DESCRIPTION

DATE

SIZE

A4

REV. A0

FILE NAME: 1150XXXX

2-155

9

10