

In This Section...

EZCODE®

Overview.....	I-2-I-3
EZL™-100 Thermal Label Printer.....	I-4
EZL-75 Thermal Label Printer & EZL Printer Labels	I-5
Printable Markers	I-6
Wire Marker Books	I-7-I-9
Wire Marker Cards — Vinyl Cloth.....	I-10-I-16
Wire Marker Cards — Vinyl Self-Laminating	I-17
Conduit & Voltage Marker Cards	I-18
Industrial Marker Cards	I-19
Wire Marker Dispenser	I-20
Vinyl Sleeve & Clip-On Markers	I-21
Stainless Steel I.D. Tag Products	I-22-I-23
Color-Coded I.D. Tapes	I-24
Barricade & Utility Warning Tapes	I-25
Accident Prevention Tags	I-26-I-27
Electrical Safety Labels	I-28-I-29
Safety Signs	I-30
Custom Sign Express Order Form	I-31
Tool Services	I-32

EZCODE®

Thomas & Betts

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

www.tnb.com

EZCODE®

Overview

Trust E-Z-Code® products to identify, secure and alert!

Perfect for the following applications:

- Industrial Construction
- In-Plant Operations
- Telecommunications
- Computer Installations
- Power Facilities
- Transportation
- Panel Equipment

Wherever electrical and electronic components and systems are used to connect, fasten, insulate, and identify wire and conduits, you'll find a Thomas & Betts quality product performing to industry-wide standards of excellence. For more than 100 years, Thomas & Betts has developed the products you need, with the quality you demand and at the right price.

E-Z-Code® Identification Products are marketed nationally through an exclusive network of authorized stocking distributors, where emphasis is placed on customer service, experience, and product knowledge. Staffed by trained professionals with a background in federal, state, and local codes and regulations, your local T&B distributor can provide you with quotation service, up-to-date pricing, shipping costs, and competitive product line evaluations when needed.



Automated Wire Markers & Accessories

The new E-Z-Code® EZL-100® Wire Marker Printer is one of the most innovative portable wire marker printers in the industry. It's a simple, easy-to-use, and reliable tool that'll have you marking wires almost as soon as you pull it from the box.

E-Z-Code® Labeling Software is a full-featured labeling system for creating custom labels tailored to your cabling and wire marking needs.



Thomas & Betts

www.tnb.com

United States

Tel: 901.252.8000

800.816.7809

Fax: 901.252.1354


Technical Services

Tel: 888.862.3289




Wire Marker Book, Cards, and Labels

Pocket pack wire marker books are easy to carry and easy to use. Wire marking is simple, clean, and fast...just pull tape out, tear, and wrap. The compact size fits in your pocket!



EZCODE®



Coming Soon!

Lockout/Tagout

Thomas & Betts offers an inclusive product line to supply the general requirements of the OSHA Lockout/Tagout standard. From comprehensive training videos to circuit breaker locking devices, E-Z-Code® Lockout/Tagout products help ensure that general industry workers will be protected from accidents during maintenance and servicing of equipment.

Coming Soon – All New E-Z-Code® Lockout/Tagout Products!

Thomas & Betts is currently revamping its complete line of E-Z-Code® lockout/tagout devices, which will be included in our next catalog. In the meantime, please contact Technical Services for product information.

T&B Technical Services
888-862-3289

Identification Tapes

Bright colors are not the only advantages of these Barricade and Burial Tapes. T&B's attention-getting tapes are also inexpensive and easy to handle. Protect-A-Line™ tape is ideal for marking hazardous or off-limit barricade areas. A large assortment of Buried Utility Tape and Foil-Backed Detectable Buried Utility Tapes help prevent potential accidents during excavations and underground installations.



Electrical Hazard Safety Signs

T&B provides a large assortment of necessary Electrical Hazard Safety Signs to complete your construction and maintenance projects. Choose from either aluminum, plastic, or self-sticking material to suit your environments. Or create your own sign to your specifications by ordering from our **Specials Form** on **page I-31**.

EZCODE®

EZL-100 Thermal Label Printer

EZ as 1-2-3...press, type, and print!

EZL-100® Thermal Label Printer

- One-touch hotkeys create labels instantly for wire wrapping, terminal blocks, device covers, patch panels, and labels in a series
- Symbols for common electrical and datacom applications, including ohm, ground, phone, data, and fax
- Five print sizes including XS, S, M, L, and XL
- Horizontal and vertical print orientation
- Automatically underlines the number 9 to prevent confusion on wire and cable
- Memory stores up to eight custom labels and automatically recalls last label
- Auto-shutoff saves battery life by turning printer off after five minutes (if idle)
- Backlit display can be turned on or off for use in low lighting conditions
- Multiple line printing of up to four lines per label
- Barcode printing of two of the most commonly used barcodes — Code-39 and Code-128
- Durable/non-smearing thermal transfer technology
- Multiple power sources uses six "AA" batteries or AC adapter (not included)
- Large display with 2-line x 15-character views (30 total)



Large, Backlit Display

One-Touch Hot Keys

Electrical and Datacom Symbols

Rugged Printer Construction with Rubber Boot Included

1 Press



2 Type



3 Print



...and that's it!



At last, a label printer designed for electricians and the way they work! T&B's new EZL-100 Label Printer packs everything you need to make wire marking fast and simple.

T&B's EZL-100 printer features handy "Hot Keys," a one-touch method to make labels for wire wrapping, patch panels, labels in a series, terminal blocks, and more. There are also common electrical and datacom symbols at your touch. And its rugged design ensures years of use.

Best of all, our permanent-adhesive labels won't smear. You'll wrap up your job with attractive, easy-to read wire labels that'll make your work easier and safer. All for a price that's easy on your wallet.

Specifications

- Dimensions: 4.5" (114mm) W x 8.3" (212mm) H x 2.8" (70mm) D
- Weight: 2.0 lbs. (890 grams)
- Power: 9V DC, using 6 "AA" batteries or AC adapter

CAT. NO.	DESCRIPTION
EZL-100	Printer (includes (1) ¼" white nylon, quick-load cassette tape, quick start card, and user manual). AC power adapter not included
EZL-100-KIT	Kit (includes EZL-Case, EZL-100 Printer (1), EZ-MP34 (1) and EZ-WN34, (1) tape, EZL-ADP adapter, and batteries
EZL-100-CASE	Hard Case for EZL-100 Printer
EZL-ADP	Adapter for EZL-100 Printer 9V, 1.5A

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

EZL-75 Thermal Label Printer and EZL Printer Labels



Quick and cost-effective labeling solution!

EZL-75 Thermal Label Printer

If your labeling needs don't quite justify all the high-end features of T&B's EZL-100 printer, now there's a lower cost solution for simple labeling. The EZL-75 thermal label printer is just as easy to use as the EZL-100 printer. Simply type and print. Or don't even bother typing. Instead, use hot keys to choose among the EZL-75 printer's built-in library of symbols and more than 150 commonly used words for security, location and voice/data/video labeling.



- Hot keys provide one-touch flagging for wires and cables and fixed-length labels for faceplates and security panels
- Incremental alpha and numeric printing makes printing distribution panel labels fast and simple
- 13-character backlit display enhances readability
- Multiple line printing supports up to 2 lines per label
- Durable bumper safeguards against damage in the tool box
- Uses the same label cassettes (up to 1/2" width) as the EZL-100 printer

Specifications

- Dimensions: 4.5" (114mm) W x 7.5" (191mm) H x 2.1" (53mm) D
- Power: 9V DC, using 6 "AA" (not included) batteries or AC adapter
- Weight: 0.8 lbs. (363 grams)


CAT. NO.	DESCRIPTION
EZL-75	Printer (includes (1) 1/2" white nylon quick-load cassette tape, quick start card, and user manual. AC power adapter not included)
EZL-ADP	Adapter for EZL-75 Printer 9V, 1.5A

Surface Applications		Vinyl and Flex Nylon	Perm. Polyester	Heat Shrink
Wire		•		•
Cable		•		•
Curved		•		
Smooth		•	•	
Flat		•	•	
Textured		•	•	
Highly Textured		•		
Length		11.5'	18.0'	5.0"
Width		1/2", 3/4"	3/8", 1/2"	1/4", 3/8"
		3/4"	3/4"	1/2", 3/4"

High-performance labels that last!

Wire Marker Labels for EZL Printers

- Perfect for wire and cable
- Print heat-shrink sleeves on the spot!
- Clear, non-smudging lettering
- Chemical/solvent resistant
- Available in yellow, white, and metallic markers
- Flame retardant, Polyolefin material, 3:1 shrink ratio
- Easy-to-peel, split-back design



Easy barcode printing!

CAT. NO.	LABEL SIZE (IN.)	RECOMMENDED WIRE SIZE (AWG)	LENGTH
Clear Polyester			
EZ-CP12	1/2"	Flat Applications Only	18'
EZ-CP34*	3/4"	Flat Applications Only	18'
Red Vinyl			
EZ-RV34*	3/4"	Any	18'
White Permanent Polyester			
EZ-WP38	3/8"	Flat Applications Only	18'
EZ-WP12	1/2"	Flat Applications Only	18'
EZ-WP34*	3/4"	Flat Applications Only	18'
Metallic Permanent Polyester			
EZ-MP38	3/8"	Flat Applications Only	18'
EZ-MP12	1/2"	Flat Applications Only	18'
EZ-MP34*	3/4"	Flat Applications Only	18'
White Flexible Nylon			
EZ-WN12	1/2"	Any	12.5'
EZ-WN34*	3/4"	Any	12.5'
Yellow Flexible Nylon			
EZ-YN12	1/2"	Any	12.5'
EZ-YN34*	3/4"	Any	12.5'

Heat-Shrink White Polyolefin Labels

EZ-WHS14	1/4"	10 - 16	5'
EZ-WHS38	3/8"	6 - 14	5'
EZ-WHS12	1/2"	4 - 6	5'
EZ-WHS34*	3/4"	2 - 4	5'

Heat-Shrink Yellow Polyolefin Labels

EZ-YHS14	1/4"	10 - 16	5'
EZ-YHS38	3/8"	6 - 14	5'
EZ-YHS12	1/2"	4 - 6	5'
EZ-YHS34*	3/4"	2 - 4	5'

Order in multiples of 5 cassettes.
* Labels fit EZL-100 printer only.

EZCODE®

Printable Markers

Print your own markers
to *your* requirements!

Laser Printable



- Self-laminating markers have a clear overlay of polyester that protects the legend against oils, grease, water, chemicals, and foreign matter
- Markers feature a strong adhesive for maximum adhesion to the wire and are available in a variety of sizes, both as standard and specials
- 1 Mil Polyester (same material as WPR rolls)
- Test template included with each 25 pack
- Sizes to suit most applications

CAT. NO.	SHEET SIZE	MARKERS PER SHEET	MARKER SIZE	PRINT AREA W x L	MAX. WIRE DIA.
WLP-1112	8½" x 11"	48	1" x 1½"	½" x 1"	5/16"
WLP-1214	8½" x 11"	32	1" x 2¼"	1" x ¾"	15/32"
WLP-12112	8½" x 11"	96	½" x 1½"	½" x ½"	5/16"
WLP-12214	8½" x 11"	64	½" x 2¼"	½" x ¾"	15/32"
WLP-12300	8½" x 11"	48	½" x 3"	½" x 1"	7/8"
WLP-1300	8½" x 11"	24	1" x 3"	1" x 1"	7/8"
WLP-1500	8½" x 11"	16	1" x 5"	1" x 1"	1¼"
WLP-2112	8½" x 11"	24	2" x 1½"	2½" x 2"	5/16"
WLP-2214	8½" x 11"	16	2" x 2¼"	2" x ¾"	15/32"
WLP-2300	8½" x 11"	12	2" x 3"	2" x 1"	7/8"
WLP-2500	8½" x 11"	8	2" x 5"	2" x 1"	1¼"

Order multiple 25 sheets.

Add suffix **A** for 500 sheets, **B** for 1,000 sheets.

WLP labels may be used on any standard laser printer.

PC Label Software

- Create, maintain and print custom labels
- Wire and cable marking
- Control panel and component marking
- Voice and data equipment marking
- Alphanumeric serialization



CAT. NO.	DESCRIPTION	STD. PKG. QTY.
EZ-CODE 1.0	E-Z-Code® PC Label Software	1

Dot-Matrix Printer Labels

CAT. NO.	SHEET SIZE	MARKERS PER SHEET	MARKER SIZE W x L	PRINT AREA W x L	MAX WIRE DIA.
WES-12112	9½" x 8"	64	½" x 1½"	½" x ½"	5/16"
WES-1112	9½" x 8"	32	1" x 1½"	1" x ½"	5/16"
WES-2112	9½" x 8"	16	2" x 1½"	2" x ½"	5/16"
WES-12214	9½" x 9"	48	½" x 2¼"	½" x ¾"	15/32"
WES-1214	9½" x 9"	24	1" x 2¼"	1" x ¾"	15/32"
WES-2214	9½" x 9"	12	2" x 2¼"	2" x ¾"	15/32"
WES-12334	9½" x 9"	32	½" x 3¾"	½" x 1"	7/8"
WES-1334	9½" x 9"	16	1" x 3¾"	1" x 1"	7/8"
WES-2334	9½" x 9"	8	2" x 3¾"	2" x 1"	7/8"
WES-2512	9½" x 12"	8	2" x 5½"	2" x 1"	1½"
WES-2128	9½" x 9"	3	2½" x 8½"	2½" x 2"	2"

Order multiple 25 sheets.

WES labels may be used on any standard dot matrix printer.

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289



Markers that withstand oil, water and humidity!

Vinyl Cloth, Standard Books

- Choose the numbers or letters you need
- Wide selection of sizes and legends
- Size 3" x 5" (76 mm x 146 mm)
- Material: vinyl cloth
- Cover keeps markers clean
- Books are 3" x 5½" pocket size
- 10 pages per book

Easy to Use!

Pocket pack wire marker books are easy to carry, and easy to use. The material is an all-purpose vinyl coated cloth tape exclusively designed to resist abrasion, oil, water, and dirt.

From Thomas & Betts you get the one-piece wire marker and terminal marker. A slight die-cut enables you to easily remove the terminal marker if you need it or leave it in place for a longer marker.



EZCODE®

CAT. NO.	NUMBER OF MARKERS AND LEGENDS
WM-0 THRU 9	40 Markers each: 0 thru 9; 10 Markers each: T1, T2, T3, L1, L2, L3
WM-0-9M	46 Markers each page; full page of 1, full page of 2, etc.
WM-0-45	10 Markers each: 0 thru 45
WM-46-90	10 Markers each: 46 thru 90
WM-A-Z	10 Markers each: A thru Z, +, -, and 0 thru 15
WM-123	150 Markers each: 1, 2, 3
WM-ABC	150 Markers each: A, B, C
WM-A-33	10 Markers each: 1 thru 33, A, B, C, +, -, T1, T2, T3, L1, L2, L3
WM-A-90	6 Markers each: 0 thru 15; 4 Markers each: 1
WM-0 THRU WM-9	6 thru 90: 2 Markers each; A thru Z 460 Markers each of any number 0 thru 9
WM-A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T, OR X	460 Markers each of any letter: -A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T or X
WM-GRD	120 Markers: ⅞" x 2½" or 240 Markers ⅞" x 1¼" with "GRD" legend
WMLC-1	24 Legends, 2 legends each per page, 480 Markers per book for house wiring and circuit breakers; ⅞" x 1½" (16mm x 10mm)

Order multiple 10 books

CAT. NO.	NUMBER OF MARKERS AND LEGENDS
WM-T3	10 Pages T ₁ , T ₂ , T ₃ ; 140 Markers ea.; total 420
WM-L3	10 Pages L ₁ , L ₂ , L ₃ ; 140 Markers ea.; total 420
WM-9T	3 Pages 1, 2, 3; 42 Markers ea.; 3 Pages A, B, C; 42 Markers ea.; 2 Pages T ₁ , T ₂ , T ₃ ; 28 Markers ea.; 2 Pages L ₁ , L ₂ , L ₃ ; 28 Markers ea.; total 140
WM-1-30	10 Pages 1-30; 14 Markers ea.; total 140
WM-12	A-Z 8½ Pages, 14 Markers ea.; Blank Write Ons 1 Page, 22 Markers ea.; Plus & Minus ⅞ Page, 7 Markers ea.; total 393
WM-13	Plus & Minus, AC, DC, 1 Page ea., 46 Markers ea.; Pos. Neg. Gnd. 1 Page ea., 28 Markers ea.; Spare, Neut. 1 Page ea., 22 Markers ea.; Blank Write-Ons 1 Page ea., 22 Markers ea.; total 256
WM-0-90	5 Pages ea. 0-45; 5 Markers ea.; 5 Pages ea. 46-90; 5 Markers ea.; total 455

EZCODE®

Wire Marker Books



EZCODE®



A handy solution for your identification needs!

E-Z-Code® Compact Wire Marker Books

- Compact books are easier to carry
- Bold letters/numbers, easy to apply and read
- Convenient alphanumeric and loadcenter legends
- E-Z-Snap feature removes the entire sheet more easily from the booklet
- Vinyl coated cloth


CAT. NO.	NUMBER OF MARKERS AND LEGENDS
----------	-------------------------------

WCMB-0-9	128 markers 0-9, ABC, +, -, marker size ¼" x 1½"
----------	--

WCMB-LC	176 markers Loadcenter Labels; marker size 1½" x ¾"
---------	---

Order multiple 20 books.

Identify and protect all in one!



Vinyl Self Laminating Books

- Convenient Alphanumeric Legends
- Lamination keeps markers protected

CAT. NO.	NUMBER OF MARKERS AND LEGENDS
----------	-------------------------------

WMSL 1-33, A-G	400 Markers: ¼" x 1¼" – printed area ¾"; 10 markers each: 1 thru 33 and A thru G
----------------	--

WMSL-0-9	40 Markers each 0 thru 9; 10 Markers each: T1, T2, T3, L1, L2, L3
----------	---

WMSL-0-45	10 Markers each 0 thru 45
-----------	---------------------------

WMSL-46-90	10 Markers each 46 thru 90
------------	----------------------------

WMSL-A-Z	10 Markers each: A thru Z; +, -, and 0 thru 15
----------	--

WMSL-A-90	6 Markers each: 0 thru 15; 4 markers each 16 thru 90; 2 markers each A thru Z
-----------	---

Vinyl Self Laminating, Blank Write-on Books

- Choose from a variety of marking area sizes
- Clear area covers print legend for extra protection
- Lamination keeps markers protected

CAT. NO.	NUMBER OF MARKERS AND LEGENDS
----------	-------------------------------

WM-BW3	30 markers 1" x 6" blank write-on self-laminating markers; marking area: 1" x 1"
--------	--

WM-BW5	60 markers 1" x 3" blank write-on, self laminating markers; marking area: 1" x ¾"
--------	---

WM-BW12	200 markers ½" x 1¼" blank write-on, self laminating markers; marking area: ½" x ¾"
---------	---

WM-BW14	400 markers ¼" x 1¼" blank write-on, self-laminating markers; marking area: ¼" x ¾"
---------	---



WM-BW34	120 markers ¾" x 1¾" blank write-on, self-laminating markers; marking area: ¾" x ½"
---------	---

Vinyl Self Laminating, Standard Laminator Book

- Protect labels or apply over non-sticking markers
- 50, 3½" x 5" clear cable laminators

CAT. NO.	NUMBER OF MARKERS AND LEGENDS
----------	-------------------------------

WM-LAM	50, 3½" x 5" Clear Cable Laminators
--------	-------------------------------------



Thomas & Betts


www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289



Vinyl, Color Coding Standard Books




- Available in two sizes
- Color your wires for coding and other applications

CAT. NO.	NUMBER OF MARKERS AND LEGENDS
WM-COL14	460 Markers each: 1/4" x 1 1/4" 1 page yellow and blue; 2 pages red, white, green, and black
WM-COL1	50 Markers each: 1" x 2 1/4" 1 page yellow and blue; 2 pages red, white, green, and black

Stay ready for quality control!

Polyolefin E-Z-Code® Pocket Pack Markers

- Easy to carry — marker books fit in shirt pocket
- Easy to use — just peel the marker from the page
- Clean and convenient — markers are tabbed so fingers never touch the adhesive



CAT. NO.	LEGENDS 240 IDENTICAL PER BOOK
WTMP-1B	CALIBRATED (black)
WTMP-2B	CERTIFICATION (black)
WTMP-3B	MAINTENANCE (blue)
WTMP-4B	REJECTED (red)
WTMP-5B	ACCEPTED (green)
WTMP-6B	HOLD (red)
WTMP-7B	RETURN TO VENDOR (orange)
WTMP-8B	REWORK (black)
WTMP-9B	HOLD FOR INSPECTION (blue)
WTMP-11B	CAUTION (black)
WTMP-16B	DATE INSTALLED (black)
WTMP-18B	DUE FOR INSPECTION (orange)
WTMP-19B	DO NOT USE AFTER (red)
WTMP-20B	INSPECTED (black)
WTMP-21B	BLANK HEADING
WTMP-22B	REPAIRED BY (orange)
WTMP-24B	SCRAPPED (orange)
WTMP-25B	TESTED (green)
WTMP-26B	CALIBRATION (green)
WTMP-52B	PROPERTY TAG (black)
WTMP-53B	SERIAL NO. (black)
WTMP-55B	TOOL NO. (blue)

15 pages per book, 16 markers per page. Each label is 1 1/4" x 5/8".
Each book contains 240 identical labels.

EZCODE®

Wire Marker Cards — Vinyl Cloth

Marker Cards repel oil, water, and humidity!

- Select from a variety of number and letter combinations and sizes
- Material — vinyl cloth
- Standard length 1½"
- Available in ¾" length

Catalog Numbering System

Example:

WC **100** **S** = Wire Marker Card,
Legend 100,
1½" Size

Y Replace Y with length


S = 1½"

D = ¾"

X Replace X with legend
Single character = 1, 2, 3 etc.
Sequence = 1 thru 33

W() Replace () with card type
C = Wire Marker Card
S = Vinyl Self-laminating

Solid Numbers




CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WCZEROS	0	36	72
WC1S, WC2S THRU WC99S	1,2,...99	36	72
WC101S, WC102S THRU WC600S	101, 102...600	25	50

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last S in the part number with a D.

Numbers in Sequence




CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WC1-THRU-33S	1-33	33	66
WC34-THRU-66S	34-66	33	66
WC67-THRU-99S	67-99	33	66
WC100-THRU-124S	100-124	25	50
WC125-THRU-149S	125-149	25	50
WC974-THRU-999S	974-999		

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last S in the part number with a D, e.g., WC1S would become WC1D.

Numbers in Sequence Repeated



CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WC1-THRU-3S	1-3	36	72
WC1-THRU-4S	1-4	36	72
WC1-THRU-5S	1-5	35	70
WC0-THRU-10S	0-10	33	66
WC1-THRU-12S	1-12	36	72
WC1-THRU-18S	1-18	36	72
WC19-THRU-36S	19-36	36	72

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last S in the part number with a D, e.g., WC1S would become WC1D.

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

Wire Marker Cards — Vinyl Cloth



Paired Numbers in Sequence

CAT. NO.	LEGEND	PAIRS OF MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WC1 THRU 16PS	1-16	16	32
WC17 THRU 32PS	17-32	16	32
WC33 THRU 48PS	33-48	16	32

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Suffix Numbers

- Use to extend numbers or to make alpha-numeric codes (i.e. adding suffix 05 to ABC=ABC05)

CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WC00S	00	36	72
WC01S, WC02S THRU WC09S	01, 02-09	36	72
WC0009S	00-09	30	60

Catalog No. WC0009S has three sequences of 00...09 on a card. WC0009D has six sequences of 00...09 on a card.

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Solid Numbers on a Colored Background

- Blue, green, red, black and brown markers have white legends; orange and yellow markers have black legends.

CAT. NO.	LEGEND	BACKGROUND COLOR	MARKERS PER CARD	
			1½" (38 MM)	¾" (19 MM)*
WCBZEROS	0	Blue	36	72
WCB1S...WCB150S	1...50	Blue	36	72
WCGZEROS	0	Green	36	72
WCG1S...WCG150S	1...50	Green	36	72
WCOZEROS	0	Orange	36	72
WCO1S...WCO150S	1...50	Orange	36	72
WCRZEROS	0	Red	36	72
WCR1S...WCR150S	1...50	Red	36	72
WCYLZEROS	0	Yellow	36	72
WCYL1S...WCYL150S	1...50	Yellow	36	72

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Numbers in Sequence on a Colored Background

CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
<i>On Black, White Characters</i>			
WCBK1-33S	1-33	33	66
WCBK34-66S	34-66	33	66
WCBK67-99S	67-99	33	66
WCBK100-124S	100-124	25	50

On Blue, White Characters

WCBL1-33S	1-33	33	66
WCBL34-66S	34-66	33	66
WCBL67-99S	67-99	33	66
WCBL100-124S	100-124	25	50

On Brown, White Characters

WCBR1-33S	1-33	33	66
WCBR34-66S	34-66	33	66
WCBR67-99S	67-99	33	66
WCBR100-124S	100-124	25	50

On Green, White Characters

WCGR1-33S	1-33	33	66
WCGR34-66S	34-66	33	66
WCGR67-99S	67-99	33	66
WCGR100-124S	100-124	25	50

On Red, White Characters

WCRD1-33S	1-33	33	66
WCRD34-66S	34-66	33	66
WCRD67-99S	67-99	33	66
WCRD100-124S	100-124	25	50

On Orange, Black Characters

WCOR1-33S	1-33	33	66
WCOR34-66S	34-66	33	66
WCOR67-99S	67-99	33	66
WCOR100-124S	100-124	25	50

On Yellow, Black Characters

WCYL1-33S	1-33	33	66
WCYL34-66S	34-66	33	66
WCYL67-99S	67-99	33	66
WCYL100-124S	100-124	25	50

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

EZCODE®

Wire Marker Cards — Vinyl Cloth

Solid Letters




CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WCAS	A	36	72
WCB5...WCZ5	B...Z	36	72
WCLAS	a	36	72
WCLB5...WCLZ5	b...z	36	72

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Letters in Sequence




CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WCAZAJ5	A thru Z plus A thru J	36	72
WCAZ09S	A thru Z plus 0 thru 9	36	72
WCLAZAJ5	a thru z plus a thru j	36	72

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Letters in Sequence on a Colored Background




CAT. NO.	LEGEND A-Z AND A-J	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WCBKA-ZS	Black (White legend)	36	72
WCBLA-ZS	Dark Blue (White legend)	36	72
WCBRA-ZS	Brown (White legend)	36	72
WCGRA-ZS	Dark Green (White legend)	36	72
WCRDA-ZS	Red (White legend)	36	72
WCORA-ZS	Orange (Black legend)	36	72
WCYLA-ZS	Yellow (Black legend)	36	72

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Solid Letters and Numbers




CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WCA1S...WCA5S	A1...A5	36	72
WCB1S...WCB5S	B1...B5	36	72
WCC1S...WCC5S	C1...C5	36	72
WCD1S...WCD5S	D1...D5	36	72
WCE1S...WCE5S	E1...E5	36	72
WCF1S...WCF4S	F1...F4	36	72
WCG1S...WCG4S	G1...G4	36	72
WCH1S...WCH5S	H1...H5	36	72
WCJ1S...WCJ4S	J1...J4	36	72
WCK1S...WCK4S	K1...K4	36	72
WCL1S...WCL5S	L1...L5	36	72
WCM1S...WCM5S	M1...M5	36	72
WCP1S...WCP4S	P1...P4	36	72
WCR1S...WCR5S	R1...R5	36	72
WCS1S...WCS5S	S1...S5	36	72
WCT0S...WCT9S	T0...T9	36	72
WCT10S...WCT15S	T10...T15	26	72
WCU1S...WCU2S	U1...U2	36	72
WCV1S...WCV2S	V1...V2	36	72
WCW1S...WCW2S	W1...W2	36	72
WCX1S...WCX4S	X1...X4	36	72
WCY1S...WCY4S	Y1...Y4	36	72
WCZ1S...WCZ4S	Z1...Z4	36	72

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Voltage Markers



CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WC3VS	3V	36	72
WC6VS	6V	36	72
WC12VS	12V	25	50
WC24VS	24V	25	50
WC110VS	110V	22	44
WC115VS	115V	22	44
WC120VS	120V	22	44
WC125VS	125V	22	44
WC180VS	180V	22	44
WC220VS	220V	22	44
WC230VS	230V	22	44
WC240VS	240V	22	44
WC270VS	270V	22	44
WC280VS	280V	22	44
WC440VS	440V	22	44
WC460VS	460V	22	44
WC480VS	480V	22	44

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Thomas & Betts

www.tnb.com


United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

Wire Marker Cards — Vinyl Cloth



Solid Symbols — Miscellaneous Electrical Symbols




CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WCPLSS	+	36	72
WCMINS	-	36	72
WCAPLSS	A+	25	50
WCAMINS	A-	25	50
WCBPLSS	B+	25	50
WCBMINS	B-	25	50
WCPSS	POS	25	50
WCNEGS	NEG	25	50
WCPHS	Phase	18	36
WCPHAS	Phase A	18	36
WCPHBS	Phase B	18	36
WCPHCS	Phase C	18	36
WC1PHS	1 Phase	18	36
WC2PHS	2 Phase	18	36
WC3PHS	3 Phase	18	36
WCINS	IN	36	72
WCOUTS	OUT	25	50
WCHOTS	HOT	25	50
WGRDS	GRD	25	50
WCNEUTS	NEUT	22	44
WCLINES	LINE	22	44
WCLPLS	L+	25	50
WCLMIS	L-	25	50
WCLOADS	LOAD	22	44
WCPUS	PU	36	72
WGRCS	⎓	36	72
WGENS	GEN	25	50
WCACS	AC	36	72
WCDCS	DC	36	72
WCCOMS	COM	25	50
WCBATS	BAT	25	50
WCBBS	BB	36	72
WCBBS	CB	36	72
WCCTS	CT	36	72
WCIGNS	IGN	25	50
WCSIGS	SIG	25	50
WCSECS	SEC	25	50
WCPSS	PS	36	72
WCPRI	PRI	25	50
WCPLS	PL	36	72
WCTBS	TB	36	72
WCSSS	SS	36	72
WCSPARES	SPARE	18	36
WCYSS	~	36	72
WGRSS	⎓	36	72
WCPE	PE	36	72
WCPENS	PEN	25	50
WC1US	1U	36	72
WC2US	2U	36	72
WC1VS	1V	36	72
WC2VS	2V	36	72
WC1WS	1W	36	72
WC2WS	2W	36	72

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Solid Machine Tool Markers




CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WC1L1S	1L1	25	50
WC1L2S	1L2	25	50
WC1L3S	1L3	25	50
WC2L1S	2L1	25	50
WC2L2S	2L2	25	50
WC2L3S...WC6L1S	2L3...6L1	25	50
WC6L2S	6L2	25	50
WC6L3S	6L3	25	50
WC1T1S	1T1	25	50
WC1T2S	1T2	25	50
WC1T3S	1T3	25	50
WC2T1S	2T1	25	50
WC2T2S	2T2	25	50
WC2T3S...WC7T1S	2T3...7T1	25	50
WC7T2S	7T2	25	50
WC7T3S	7T3	25	50
WCLL1S	LL1	25	50
WCLL2S	LL2	25	50
WCLL3S	LL3	25	50

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

Machine Tool Markers in Sequence



CAT. NO.	LEGEND	MARKERS PER CARD	
		1½" (38 MM)	¾" (19 MM)*
WC1T1-3T3S	1T1, 1T2, 1T3 2T1, 2T2, 2T3 3T1, 3T2, 3T3	27	54
WC4T1-6T3S	4T1, 4T2, 4T3 5T1, 5T2, 5T3 6T1, 6T2, 6T3	27	54
WC7T1-9T3S	7T1, 7T2, 7T3 8T1, 8T2, 8T3 9T1, 9T2, 9T3	27	54
WCLL1-LL3S	LL1, LL2, LL3	27	54
WCA1-S2S	A1, A2, F1 F2, S1, S2	36	72

Order multiple 25 cards.

*When ¾" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

EZCODE®

Wire Marker Cards — Vinyl Cloth

Mini Markers are used to identify smaller items such as terminal blocks and small wires.

Terminal Block — Mini Markers

1	2	3	4	5	6	7	8	9	10
21	26	27	28	29	30	31	32	33	34
1	2	3	4	5	6	7	8	9	10
25	26	27	28	29	30	31	32	33	34
1	2	3	4	5	6	7	8	9	10
25	26	27	28	29	30	31	32	33	34

CAT. NO.	LEGEND	MARKERS PER CARD MARKER SIZE 5/16" x 3/16"
WC1-48TM	1, 2 thru 48	144
WC49-96TM	49, 50 thru 96	144
WCA-ZTM	A, B thru Z	144

Order multiple 25 cards
A thru Z legend does not include "I" or "O"

Solid Numbers & Solid Letters — Mini Markers

2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2
2	2	2	2	2	2	2	2	2	2

A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A
A	A	A	A	A	A	A	A	A	A

CAT. NO.	LEGEND	MARKERS PER CARD 1/2" (13 MM)
Solid Numbers		
WCZEROMIN...WC99MIN	0, 1,...99	150
WC100MIN...WC250MIN	100, 101...250	99
Solid Letters		
WCAMIN	A	150
WCBMIN...WCZMIN	B,C... Z	150

Order multiple 25 cards

Numbers in Sequence — Mini Markers

2	3	4	5	6	7	8	9	10	11	12
2	3	4	5	6	7	8	9	10	11	12
1	2	3	4	5	6	7	8	9	10	11
0	1	2	3	4	5	6	7	8	9	10
0	1	2	3	4	5	6	7	8	9	10
0	1	2	3	4	5	6	7	8	9	10
0	1	2	3	4	5	6	7	8	9	10
0	1	2	3	4	5	6	7	8	9	10
0	1	2	3	4	5	6	7	8	9	10
0	1	2	3	4	5	6	7	8	9	10

CAT. NO.	LEGEND	MARKERS PER CARD 1/2" (13 MM)
WC0-49MIN	0, 1... 49	150
WC50-99MIN	50, 51...99	150
WC100-132MIN	100, 101...132	99
WC133-165MIN	133, 134...495	99
THRU WC463-495MIN		

Order multiple 25 cards
Quantity of each number per card — 3

Letters in Sequence — Mini Markers

C	D	E	F	G	H	I	J	K	L	M
C	D	E	F	G	H	I	J	K	L	M
A	B	C	D	E	F	G	H	I	J	K
A	B	C	D	E	F	G	H	I	J	K
A	B	C	D	E	F	G	H	I	J	K
A	B	C	D	E	F	G	H	I	J	K
A	B	C	D	E	F	G	H	I	J	K
A	B	C	D	E	F	G	H	I	J	K
A	B	C	D	E	F	G	H	I	J	K
A	B	C	D	E	F	G	H	I	J	K
A	B	C	D	E	F	G	H	I	J	K

CAT. NO.	LEGEND	MARKERS PER CARD 1/2" (13 MM)
WCAZMIN	A, B...Z	156

Order multiple 25 cards

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354



Technical Services
Tel: 888.862.3289

Wire Marker Cards — Vinyl Cloth



Cable markers are used to identify large conductors, electrical cables and tubing for hydraulic systems!

Solid Numbers & Solid Letters — Cable Markers




CAT. NO.	LEGEND	MARKERS PER CARD	
		3½" (89 MM)	1¾" (45 MM)*
<i>Solid Letters</i>			
WCCMAS	A	18	36
WCCMBS	B	18	36
WCCMCS	C	18	36
WCCMDS	D	18	36
WCCMES	E	18	36
WCCMFS	F	18	36
WCCMNS	N	18	36
<i>Solid Numbers</i>			
WCCMOS	0	18	36
WCCM1S, WCCM2S...WCCM9S	1, 2...9	18	36

Order multiple 25 cards

* When 1 1/4" length cable markers are required, substitute the last **S** in the part number with a **D**. e.g., WCCM1S would become WCCM1D.

Numbers or Letters in Sequence — Cable Markers



CAT. NO.	LEGEND	MARKERS PER CARD	
		3 1/2" (89 MM)	1 1/4" (45 MM)*
WCCM01-09S	01 thru 09	2	4
WCCM1-9S	1 thru 9	2	4
WCCM1-18S	1 thru 18	1	2
WCCM19-36S	19 thru 36	1	2
WCCM37-54S	37 thru 54	1	2
WCCM55-72S	55 thru 72	1	2
WCCM73-90S	73 thru 90	1	2
WCCM91-99S	91 thru 99	2	4
WCCMA-IS	A thru I	2	4
WCCMJ-RS	J thru R	2	4
WCCMS-ZS	S thru Z	2	4

Order multiple 25 cards

* When 1 1/4" length cable markers are required, substitute the last **S** in the part number with a **D**. e.g., WCCM1S would become WCCM1D.


EZCODE®

Wire Marker Cards — Vinyl Cloth


Maintenance and Production Label Cards

CAT. NO.	WORDING	COLORS WHITE BACKGROUND	LABELS PER CARD	LABEL SIZE W x L
WCMP5	Accepted	Green	14	1½" x ¾"
WCMP1	Calibrated	Black	14	1½" x ¾"
WCMP26	Calibration	Green	14	1½" x ¾"
WCMP2	Certification	Black	14	1½" x ¾"
WCMP18	Due For Inspection	Orange	14	1½" x ¾"
WCMP4	Rejected	Red	14	1½" x ¾"
WCMP25	Tested	Green	14	1½" x ¾"
WCMP75	Calibration	Green	9	2¾" x 1"

Order multiple 25 cards




Blank Write-On Markers



CAT. NO.	MARKER SIZE	MARKERS PER CARD
WCBW14X34D	¼" x ¾"	72
WCBW14X112S	¼" x 1½"	36
WCBW1132X112S	1½" x 1½"	26
WCBW12X12D	½" x ½"	54
WCBW12X112S	½" x 1½"	18
WCBW58X112S	⅝" x 1½"	14
WCBW34X12D	¾" x ½"	36
WCBW34X214S	¾" x 2¼"	12
WCBW1X112S	1" x 1½"	9
WCBW112X112S	1½" x 1½"	6

Order multiple 25 cards

Solid NEMA Color Markers



CAT. NO.	COLOR	MARKERS PER LEGEND	
		1½" (38 MM)	¾" (19 MM)*
WCBLKS	Black	36	72
WCBLDS	Blue — Dark	36	72
WCBLLS	Blue — Light	36	72
WCBRNS	Brown	36	72
WCGRYS	Gray	36	72
WCDGRS	Green — Dark	36	72
WCGRLS	Green — Light	36	72
WCMARS	Maroon	36	72
WCOLIS	Olive	36	72
WCORAS	Orange	36	72
WCPINS	Pink	36	72
WCPURS	Purple	36	72
WCREDS	Red	36	72
WCTANS	Tan	36	72
WCWHIS	White	36	72
WCYELS	Yellow	36	72

Order multiple 25 cards

*When ¾" length markers are required, substitute the last S in the part number with a D, e.g., WC1S would become WC1D.

Thomas & Betts

www.tnb.com


United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

Wire Marker Cards — Vinyl Self-Laminating




Write-On Cable Markers




CAT. NO.	OVERALL MARKER SIZE	WIDTH HEIGHT WRITE-ON AREA	MARKERS PER CARD
WSLM33	1" x 2 1/4"	1" x 3/4"	3
WSLM35	1" x 5"	1" x 1"	3
WSLM123	1 1/2" x 3"	1 1/2" x 3/4"	2
WSLM23	2" x 3"	2" x 3/4"	2
WSLM125	1 1/2" x 5"	1 1/2" x 1"	2
WSLM25	2" x 5"	2" x 1"	2
WSLM48	2" x 8"	2" x 3 3/4"	2
WSLM95	2 1/4" x 2 1/4"	2 1/2" x 2 1/4"	2
WSLM410	2" x 10"	2" x 4 1/2"	2
WSLM415	2" x 15"	2" x 7"	2

Blank Write-On Markers



CAT. NO.	WRITE ON AREA (W X D)	MARKERS PER CARD 1 1/2" (38 MM)
WSBW14X112S	1/4" x 1 1/2"	36
WSBW38X112S	3/8" x 1 1/2"	26
WSBW12X112S	1/2" x 1 1/2"	18
WSBW34X112S	3/4" x 1 1/2"	12
WSBW1X112S	1" x 1 1/2"	9
WSBW112X112S	1 1/2" x 1 1/2"	6

Solid Letters




CAT. NO.	LEGEND	MARKERS PER CARD	
		1 1/2" (38 MM)	3/4" (19 MM)*
WSAS	A	36	72
WSBS...WSZS	B, C...Z	36	72

Order multiple 25 cards

* When 1 1/4" length cable markers are required, substitute the last **S** in the part number with a **D**. e.g., WCCM1S would become WCCM1D.

Solid Numbers



CAT. NO.	LEGEND	MARKERS PER CARD	
		1 1/2" (38 MM)	3/4" (19 MM)*
WSZEROS	0	36	72
WS1S...WS99S	1, 2...99	36	72
WS100S	100	25	50
WS101S...WS600S	101, 102...600	25	—

Order multiple 25 cards

When 3/4" length markers are required, substitute the last **S** in the part number with a **D**, e.g., WC1S would become WC1D.

EZCODE®

Conduit & Voltage Marker Cards

Identify electrical systems, including load centers, circuit breakers, switches or any other vital electrical equipment!

Vinyl Conduit and Voltage Markers

- Helps prevent mistakes and trial and error searching during electrical service work
- Manufactured of rugged Self-Sticking Vinyl with high-contrast black printing on safety orange background
- OSHA compliant



STYLE A: 2¼" x 9"
(1 marker per card) Character Height 1¼"



STYLE B: 1½" x 4½"
(4 markers per card) Character Height 7⁄8"



STYLE C: 2¼" x 1½"
(18 markers per card) Character Height 5⁄8"

STYLE A 2¼" x 9"	STYLE B 1½" x 4½"	STYLE C 2¼" x 1½"	LEGEND
WJT-5010	WDT-5010	WAT-5010	110 volts
WJT-5011	WDT-5011	WAT-5011	115 volts
WJT-5012	WDT-5012	WAT-5012	120 volts
WJT-5045	WDT-5045	WAT-5045	120/208 volts
WJT-5013	WDT-5013	WAT-5013	208 volts
WJT-5014	WDT-5014	WAT-5014	220 volts
WJT-5015	WDT-5015	WAT-5015	230 volts
WJT-5016	WDT-5016	WAT-5016	240 volts
WJT-5017	WDT-5017	WAT-5017	250 volts
WJT-5018	WDT-5018	WAT-5018	277 volts
WJT-5046	WDT-5046	WAT-5046	277/480 volts
WJT-5057	WDT-5057	WAT-5057	380 volts
WJT-5044	WDT-5044	WAT-5044	415 volts
WJT-5019	WDT-5019	WAT-5019	440 volts
WJT-5020	WDT-5020	WAT-5020	460 volts
WJT-5021	WDT-5021	WAT-5021	480 volts
WJT-5022	WDT-5022	WAT-5022	550 volts
WJT-5023	WDT-5023	WAT-5023	600 volts
WJT-5024	WDT-5024	WAT-5024	2200 volts
WJT-5025	WDT-5025	WAT-5025	2300 volts
WJT-5026	WDT-5026	WAT-5026	2400 volts
WJT-5027	WDT-5027	WAT-5027	4160 volts
WJT-5028	WDT-5028	WAT-5028	4800 volts
WJT-5058	WDT-5058	WAT-5058	5000 volts
WJT-5029	WDT-5029	WAT-5029	6900 volts

Order multiple 25 cards

STYLE A 2¼" x 9"	STYLE B 1½" x 4½"	STYLE C 2¼" x 1½"	LEGEND
WJT-5030	WDT-5030	WAT-5030	7200 volts
WJT-5059	WDT-5059	WAT-5059	12,000 volts
WJT-5060	WDT-5060	WAT-5060	13,000 volts
WJT-5047	WDT-5047	WAT-5047	13,200 volts
WJT-5031	WDT-5031	WAT-5031	13,800 volts
WJT-5032	WDT-5032	WAT-5032	AC
WJT-5043	WDT-5043	WAT-5043	Air Conditioning
WJT-5052	WDT-5052	WAT-5052	Circuit Breaker
WJT-5051	WDT-5051	WAT-5051	Circuit #___
WJT-5038	WDT-5038	WAT-5038	DC
WJT-5050	WDT-5050	WAT-5050	Electric Out of Service
WJT-5033	WDT-5033	WAT-5033	Emergency Service
WJT-5039	WDT-5039	WAT-5039	Exit Lights
WJT-5040	WDT-5040	WAT-5040	Fire Alarm
WJT-5053	WDT-5053	WAT-5053	Fuse Box
WJT-5041	WDT-5041	WAT-5041	Heating Circuit
WJT-5037	WDT-5037	WAT-5037	Lights
WJT-5042	WDT-5042	WAT-5042	Light & Power
WJT-5048	WDT-5048	WAT-5048	On/Off
WJT-5036	WDT-5036	WAT-5036	Power
WJT-5034	WDT-5034	WAT-5034	Single Phase
WJT-5055	WDT-5055	WAT-5055	Spare
WJT-5056	WDT-5056	WAT-5056	Telephone
WJT-5035	WDT-5035	WAT-5035	Three Phase
WJT-5054	WDT-5054	WAT-5054	___ volts

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289



Easy-to-read and available in a variety of configurations!

Vinyl Cloth Industrial Markers


- High-contrast self-sticking markers make numbering and coding jobs quick and easy
- Select character heights ranging from $\frac{5}{16}$ " to $\frac{3}{4}$ "




Series-200
10 markers per card
Marker Size: $\frac{1}{8}$ " x $2\frac{1}{4}$ "
Character Height: 2"



Series-100
10 markers per card
Marker Size: $\frac{1}{8}$ " x $1\frac{1}{2}$ "
Character Height: 1"



Series-003
78 markers per card
Marker Size: $\frac{3}{8}$ " x $\frac{1}{2}$ "
Character Height: $\frac{5}{16}$ "



Series-063
32 markers per card
Marker Size: $\frac{5}{16}$ " x $\frac{3}{4}$ "
Character Height: $\frac{5}{16}$ "

DESCRIPTION	LEGEND	CAT. NO. SERIES 003	CAT. NO. SERIES 063	CAT. NO. SERIES 100	CAT. NO. SERIES 200
LETTERS	A thru Z	WCNL003A...WCNL003Z	WCNL063A...WCNL063Z	WCNL100A...WCNL100Z	WCNL200A...WCNL200Z
NUMBERS	0	WCNL003ZERO	WCNL063ZERO	WCNL100ZERO	WCNL200ZERO
NUMBERS	1 thru 9	WCNL0031...WCNL0039	WCNL0631...WCNL0639	WCNL1001...WCNL1009	WCNL2001...WCNL2009
LETTERS IN SEQUENCE	A thru Z	WCNL003AZ	WCNL063AZ	N/A	N/A
LETTERS IN SEQUENCE	A thru J	N/A	N/A	WCNL100AJ	WCNL200AJ
LETTERS IN SEQUENCE	K thru T	N/A	N/A	WCNL100KT	WCNL200KT
LETTERS IN SEQUENCE	U thru z	N/A	N/A	WCNL100UZ	WCNL200UZ
NUMBERS IN SEQUENCE	0 thru 9	WCNL00309	WCNL06309	WCNL10009	WCNL20009

Order multiple 5 cards

Reflective Industrial Markers

CAT. NO.	SIZE	CHARACTER HEIGHT	MARKER SIZE
WRSUM*	Small	1 $\frac{1}{2}$ "	1 $\frac{3}{8}$ " x 1 $\frac{1}{8}$ "
WRUM*	Standard	2 $\frac{1}{2}$ "	1 $\frac{3}{4}$ " x 2 $\frac{1}{8}$ "
WRLUM*	Large	3 $\frac{3}{4}$ "	2 $\frac{1}{8}$ " x 4 $\frac{5}{16}$ "

* Add Letter (A-Z) or Number (0-9) desired in place of asterisk to complete CAT. NO.
Example WRSUM1, WRSUM2, WRSUMA, etc.

Order multiple 25 cards





EZCODE®


Wire Marker Dispenser

Make identification clean and fast...just pull tape out, tear and wrap!

Wire Marker Dispenser

- Compact size fits in your pocket or hangs from work belt
- Unique design enables easy access to all legends during use or when refilling
- Lifetime guarantee on T&B pack dispenser

CAT. NO.	DESCRIPTION
WDFP-0-9	Loaded Dispenser with Legends 0 thru 9
WDFP-NEMA	Loaded Dispenser with 10 NEMA colors
WDFP	Empty Dispenser



Refills — Polyester Tape

CAT. NO.	LEGEND	LABEL COLOR	ROLLS PER LEGEND
WDFPR-0	0	WHITE	10
WDFPR-1...WDFPR-9	1, 2...9	WHITE	10
WDFPR-0-9	0...9	WHITE	1
WDFPR-10-19	10...19	WHITE	1
WDFPR-A...WDFPR-Z	A, B...Z	WHITE	10
WDFPR-L1	L1	WHITE	10
WDFPR-L2	L2	WHITE	10
WDFPR-L3	L3	WHITE	10
WDFPR-T1	T1	WHITE	10

CAT. NO.	LEGEND	LABEL COLOR	ROLLS PER LEGEND
WDFPR-T2	T2	WHITE	10
WDFPR-T3	T3	WHITE	10
WDFPR-MIN	—	WHITE	10
WDFPR-PLS	+	WHITE	10
WDFPR-YEL	BLANK	YELLOW	10
WDFPR-WHT	BLANK	WHITE	10
WDFPR-BLK	BLANK	BLACK	10
WDFPR-BRN	BLANK	BROWN	10
WDFPR-BLU	BLANK	BLUE	10
WDFPR-GRN	BLANK	GREEN	10
WDFPR-RED	BLANK	RED	10

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

Vinyl Sleeve & Clip-On Markers



Permanently identify wires, cables, leads and more!

Sleeve Markers



- Facilitates the installation, repair and servicing of equipment during production or maintenance
- Available in a variety of sizes and materials to meet all your needs
- Resistant to most chemicals, oils, solvents and fungus
- Performs well in low and high temperatures

CAT. NO.	RECOMMENDED WIRE DIAMETER	AWG	STD. PKG. QTY.
SMS118*	.051-.118	22-16	10 strips of 25 markers/bag
SMS196*	.098-.196	16-10	10 strips of 25 markers/bag
SMS394*	.157-.394	10-4	10 strips of 25 markers/bag
SMS630*	.315-.630	6-00	20/Bag Loose

*To Order: Add letter, number, or symbol desired in place of asterisk to complete each Cat. No.
 Symbols: SLA = /; PLS = +; GRD = -; MIN = -; Blank = No Legend
 Other colors are available upon request. Contact tech service for availability.

Sleeve Markers — 1,000 Continuous Markers on a Reel



CAT. NO.	RECOMMENDED WIRE DIAMETER	AWG	STD. PKG. QTY.
SMR118*	.051-.118	22-16	1
SMR196*	.098-.196	16-10	1
SMD-894*	.157-.394	10-4	1

*To Order: Add letter, number, or symbol desired in place of asterisk to complete each Cat. No.
 Symbols: SLA = /; PLS = +; GRD = -; MIN = -; Blank = No Legend

Clip-On Markers



CAT. NO.	RECOMMENDED WIRE DIAMETER	AWG	STD. PKG. QTY.
SMC118*	.094-.118	18-16	200/bag attached
SMC157*	.118-.157	16-14	200/bag attached
SMC197*	.157-.197	12-10	200/bag attached
SMC244*	.197-.244	8-6	200/bag attached

*To Order: Add letter, number, or symbol desired in place of asterisk to complete each Cat. No.

Magazine Dispenser Feeds Left or Right



CAT. NO.	RECOMMENDED WIRE DIAMETER	AWG	STD. PKG. QTY.
SMPP196A	.098-.196	16-10	20 Strips of 25 Markers/dispenser
SMPT196A	.098-.196	16-10	20 Strips of 25 Markers with tool/dispenser

Legend is 0-9 for magazine dispenser

Sleeve Marker Application Tool



CAT. NO.	RECOMMENDED WIRE DIAMETER	AWG	STD. PKG. QTY.
SMAT118	.051-.118	22-16	5/bag
SMAT196	.098-.196	16-10	5/bag

EZCODE®

Stainless Steel I.D. Tag Products

Identify your cable bundles with permanent, Type 304 stainless steel imprinted tags applied with stainless steel cable ties.

I.D. Tagging System

- After imprinting the tags, merely slip a tie through slots in the tag and fasten with the installation tool
- Works with ¼" wide ties

CAT. NO.	WIDTH		LENGTH		WEIGHT	
	IN.	MM	IN.	MM	LBS.	KG
SSID100	.75	19.05	2.0	51	0.5	.22
SSID101	1.50	38.10	2.5	63	1.2	.55
SSID102	.75	19.05	3.5	89	0.8	.36

304 Stainless Steel

Packaging Quantity: 100/box

.015" (.254mm) Thickness

NOTE: Customized pre-embossed tags are available. Please consult Customer Service for details.

Add suffix (316) for 316 Stainless Steel.


Imprints Thomas & Betts stainless steel I.D. tags.

I.D. Tag Imprinter

- Includes special tag holder that provides quick, accurate positioning of tag
- Comes with a ¾" character imprinting wheel

CAT. NO.	DESCRIPTION	WEIGHT	
		LBS.	KG
WTID200	I.D. Tag Imprinter	29.5	13.41
WTID281	¾" Character Imprinting Wheel	—	—
WTID283	⅝" Character Imprinting Wheel	—	—
WTID290	¾" Character Imprinting Wheel	—	—

Packaging Quantity: 1/box



Thomas & Betts

www.tnb.com

United States

Tel: 901.252.8000

800.816.7809

Fax: 901.252.1354

Technical Services

Tel: 888.862.3289


Stainless Steel I.D. Tag Products



A complete range of individual letters, numbers and symbols!

Thomas & Betts Stainless Steel I.D. Tag

- Slip them over carriers or strips (shown **below**) and attach to your cable or hose with a variety of Thomas & Betts Stainless Steel Cable Ties



EZCODE®

CAT. NO.	DESCRIPTION	LENGTH	WIDTH	STD. PKG.	WT. PER 100
ER010	A	.445"	.375"	100	.31
ER011	B	.445"	.375"	100	.31
ER012	C	.445"	.375"	100	.31
ER013	D	.445"	.375"	100	.31
ER014	E	.445"	.375"	100	.31
ER015	F	.445"	.375"	100	.31
ER016	G	.445"	.375"	100	.31
ER017	H	.445"	.375"	100	.31
ER018	I	.445"	.375"	100	.31
ER019	J	.445"	.375"	100	.31
ER020	K	.445"	.375"	100	.31
ER021	L	.445"	.375"	100	.31
ER022	M	.445"	.375"	100	.31
ER023	N	.445"	.375"	100	.31
ER024	O	.445"	.375"	100	.31
ER025	P	.445"	.375"	100	.31
ER026	Q	.445"	.375"	100	.31
ER027	R	.445"	.375"	100	.31
ER028	S	.445"	.375"	100	.31
ER029	T	.445"	.375"	100	.31
ER030	U	.445"	.375"	100	.31

CAT. NO.	DESCRIPTION	LENGTH	WIDTH	STD. PKG.	WT. PER 100
ER031	V	.445"	.375"	100	.31
ER032	W	.445"	.375"	100	.31
ER033	Y	.445"	.375"	100	.31
ER034	Z	.445"	.375"	100	.31
ER018	1	.445"	.375"	100	.31
ER037	2	.445"	.375"	100	.31
ER038	3	.445"	.375"	100	.31
ER039	4	.445"	.375"	100	.31
ER040	5	.445"	.375"	100	.31
ER041	6	.445"	.375"	100	.31
ER021	7	.445"	.375"	100	.31
ER042	8	.445"	.375"	100	.31
ER041	9	.445"	.375"	100	.31
ER024	0	.445"	.375"	100	.31
ER035	Minus/Hyphen	.445"	.375"	100	.31
ER036	Blank	.445"	.375"	100	.31
ER046	Plus +	.445"	.375"	100	.31
ER047	Earth	.445"	.375"	100	.31
ER048	Sine	.445"	.375"	100	.31
ER049	Slash /	.445"	.375"	100	.31

Character size .218"
Material .025 316 stainless steel

Convenient and easy identification!

Thomas & Betts Stainless Steel I.D. Tag Carriers/Strips

- Select from carriers and strips
- Tag kit contains 50 of each letter, number, symbol, carrier and strip in a handy carrying case



CAT. NO.	DESCRIPTION	LENGTH	WIDTH	STD. PKG.	WT. PER 100
ER043	6 Character Carrier	3.64"	.38"	100	.73
ER044	10 Character Carrier	5.14"	.38"	100	1.25
ER045	16 Character Carrier	7.39"	.38"	100	1.47
ER050	Short Strip	4.25"	.38"	100	.98

CAT. NO.	DESCRIPTION	LENGTH	WIDTH	STD. PKG.	WT. PER 100
ER051	Medium Strip	5.75"	.38"	100	1.33
ER052	Long Strip	8.0"	.38"	100	1.85
ER060	I.D. Tag Kit	—	—	1	—

I.D. Tag Kit contains 50 of each letter, number, symbol, carrier, and strip in a handy carrying case.



EZCODE®

Color-Coded I.D. Tapes

Save time and money over painting!

Color-Coded Vinyl I.D. Tape

- Effectively warns or identifies equipment, traffic and housekeeping items
- Choose from different widths
- Many colors available



1" WIDE CAT. NO.	2" WIDE CAT. NO.	3" WIDE CAT. NO.	4" WIDE CAT. NO.	COLOR
AA-1121	BA-1121	CA-1121	NA-1121	Silver
AA-1122	BA-1122	CA-1122	NA-1122	Black
AA-1123	BA-1123	CA-1123	NA-1123	Blue
AA-1124	BA-1124	CA-1124	NA-1124	Brown
AA-1125	BA-1125	CA-1125	NA-1125	Green
AA-1126	BA-1126	CA-1126	NA-1126	Orange
AA-1127	BA-1127	CA-1127	NA-1127	Purple
AA-1128	BA-1128	CA-1128	NA-1128	Red
AA-1129	BA-1129	CA-1129	NA-1129	White
AA-1130	BA-1130	CA-1130	NA-1130	Yellow
AA-1131	BA-1131	CA-1131	NA-1131	Clear

60 yards per roll

Reflective Roll Tape



2" WIDE CAT. NO.	3" WIDE CAT. NO.	4" WIDE CAT. NO.	COLOR
AZ-3108	BZ-3108	CZ-3108	Black & Yellow Stripe
AZ-3110	BZ-3110	CZ-3110	Red & White Stripe

5 yards per roll

Self-Sticking Vinyl Cloth Tape



2" WIDE CAT. NO.	3" WIDE CAT. NO.	4" WIDE CAT. NO.	COLOR
AZ-1100	BZ-1100	CZ-1100	Black & Yellow Stripe
AZ-1102	BZ-1102	CZ-1102	Red & White Stripe
AZ-1303	BZ-1303	CZ-1303	Magenta & Yellow Stripe & Radiation Symbol

30 yards per roll

Laminated Vinyl Tape



2" WIDE CAT. NO.	3" WIDE CAT. NO.	4" WIDE CAT. NO.	COLOR
AZ-2104	BZ-2104	CZ-2104	Black & Yellow Stripe
AZ-2106	BZ-2106	CZ-2106	Red & White Stripe

18 yards per roll

2 Sided Foam Mounting Tape

CAT. NO.	DESCRIPTION
NA-0365	2-Sided Foam Mounting Tape

9 yards per roll

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

Barricade & Utility Warning Tapes



Mark off hazardous or off-limit areas quickly and easily!

Protect-A-Line™ Barricade and Burial Tapes

EZCODE®



Barricade Tape

- Inexpensive and easy to handle
- Convenient and reusable
- For indoor and outdoor use



Buried Utility Tape

- Protect against costly dig-ins
- Place 1 to 1½ feet below the ground surface directly above the pipeline or cable below
- Bright, fade-resistant colors warn equipment operators that a vital pipeline or cable is buried below, before damage occurs
- Black text on a bright background



Foil Backed Detectable Buried Utility Tape

- Features a metallic backing designed to be detectable under normal earthen surfaces up to 18" with common metal detectors
- Simple and fast method for relocating lines, cables and conduit for future renovation
- Black text on a bright background

CAT. NO.	LEGEND	COLOR
----------	--------	-------

Surveyors Tape 1½" x 1,000'

NA-0200	No Legend, No Printing	Yellow
NA-0201	No Legend, No Printing	Red
NA-0202	No Legend, No Printing	Green
NA-0203	No Legend, No Printing	Blue
NA-0204	No Legend, No Printing	Orange

Barricade Tape 3" x 1,000'

NA-0250	Caution	Yellow
NA-0253	Caution Construction Area	Yellow
NA-0254	Caution Do Not Enter	Yellow
NA-0256	Caution Hard Hat Area	Yellow
NA-0257	Caution High Voltage	Yellow
NA-0258	Caution Men Working	Yellow
NA-0261	Caution Open Trench	Yellow
NA-0267	Danger, on Stripes	Red & White

Buried Utility Tape 3" x 1,000'

NA-0600	Electric Line	Red
NA-0608	Electric Line	Yellow
NA-0601	Water Line	Blue
NA-0602	Telephone Line	Orange
NA-0603	Gas Line	Yellow
NA-0605	Sewer Line	Green
NA-0606	High Voltage Line	Red
NA-0609	Fiber Optic Cable	Orange

NOTE: All barricade and utility tapes are 4 MIL polyethylene and are not self sticking. All legends are printed in black. Standard package is 1 roll.

CAT. NO.	LEGEND	COLOR
----------	--------	-------

Buried Utility Tape 6" x 1,000'

NA-0700	Electric Line	Red
NA-0708	Electric Line	Yellow
NA-0701	Water Line	Blue
NA-0702	Telephone Line	Orange
NA-0703	Gas Line	Yellow
NA-0706	High Voltage Line	Red
NA-0709	Fiber Optic Cable	Orange

Foil-Backed Detectable Buried Utility Tape 3" x 1,000'

NAF-0600	Electric Line	Red
NAF-0608	Electric Line	Yellow
NAF-0601	Water Line	Blue
NAF-0602	Telephone Line	Orange
NAF-0603	Gas Line	Yellow
NAF-0604	Oil Line	Yellow
NAF-0605	Sewer Line	Green
NAF-0606	High Voltage Line	Red
NAF-0607	Cable TV Line	Orange
NAF-0609	Fiber Optic Cable	Orange

Foil-Backed Detectable Buried Utility Tape 6" x 1,000'

NAF-0700	Electric Line	Red
NAF-0708	Electric Line	Yellow
NAF-0701	Water Line	Blue
NAF-0702	Telephone Line	Orange
NAF-0703	Gas Line	Yellow
NAF-0704	Oil Line	Yellow
NAF-0705	Sewer Line	Green
NAF-0706	High Voltage Line	Red
NAF-0707	Cable TV Line	Orange
NAF-0709	Fiber Optic Cable	Orange

EZCODE®**Accident Prevention Tags****Tags****Durable Lockout Tags**

OSHA requirements for Lockout Tags are very specific, and E-Z-Code® Lockout Tags have been designed to comply with every performance standard. Tags are available in two sturdy materials: reusable dura-tag and economical vinyl. All tags have a reinforcing brass grommet with $\frac{3}{8}$ " diameter to accept most padlocks. All tag surfaces allow employees to easily personalize tags with their name, department and estimated completion information as required by regulations.

Reusable Dura-Tag

Dura-Tags are encapsulated in matte polyester laminate. Tags withstand 80-lb. pullout force. These tags are designed for harsh plant environments and are chemically resistant. Supplied with heavy-duty $\frac{3}{8}$ " ID brass grommet and nylon ties.

Economy Polyester

Rigid polyester surface is easy to write on and stays legible longer. Wipes clean easily, ready to use again and again. Exceeds OSHA 50-lb pullout requirement. Supplied with $\frac{3}{8}$ " diameter brass grommet and nylon ties.

Reverse Side Options

Reverse Side #1



Reverse Side #2

DESCRIPTION	SIZE	GROMMET	QTY.
Reusable Dura-Tag	5½" x 3"	$\frac{3}{8}$ " Brass	25/pkg.
Economy Polyester	5¼" x 3"	$\frac{3}{8}$ " Brass	25/pkg.

**Reusable Dura-Tag**

TG65502 — Rev. Side #1

TG65503 — Rev. Side #1

TG65504 — Rev. Side #1

TG65505 — Rev. Side #1

TG65670 — Rev. Side #2

Economy Polyester

TG66050 — Rev. Side #1

TG66053 — Rev. Side #1

TG66055 — Rev. Side #1

TG66057 — Rev. Side #1

TG66052 — Rev. Side #2

Order multiple 25 tags.

**Reusable Dura-Tag**

TG65506 — Rev. Side #1

TG65515 — Rev. Side #1

TG65520 — Rev. Side #1

TG65526 — Rev. Side #1

TG65671 — Rev. Side #2

Economy Polyester

TG66059 — Rev. Side #1

TG66061 — Rev. Side #1

TG66063 — Rev. Side #1

TG66066 — Rev. Side #1

TG66065 — Rev. Side #2

Order multiple 25 tags.

Accident Prevention Tags



Tags

Reusable Dura-Tag

Dura-Tags are encapsulated in matte polyester laminate. Tags withstand 80-lb. pullout force. These tags are designed for harsh plant environments and are chemically resistant. Supplied with heavy-duty 3/16" ID brass grommet and nylon ties.

Reverse Side Options



Reverse Side #1



Reverse Side #2



DESCRIPTION	SIZE	GROMMET	QTY.
Reusable Dura-Tag	5 3/4" x 3"	3/16"	25/pkg.
Economy Polyester	5 3/4" x 3"	3/16"	25/pkg.
Card Stock Tags	5 3/4" x 3"	3/16"	25/pkg.

Economy Polyester

Rigid polyester surface is easy to write on and stays legible longer. Wipes clean easily, ready to use again and again. Exceeds OSHA 50-lb pullout requirement. Supplied with 3/16" diameter brass grommet and nylon ties.

Cardstock

Economical, yet durable cardstock. These disposable tags come with a 3/16" diameter brass grommet and a string fastener. Material accepts pen, pencil or marker writing.



Reusable Dura-Tag

TG86425 — Rev. Side 1

TG86424 — Rev. Side 1

TG86414 — Rev. Side 2

Economy Polyester

TG86544 — Rev. Side 1

TG86543 — Rev. Side 1

TG86533 — Rev. Side 2



Cardstock Tags

TG86654 — Rev. Side 1

TG86653 — Rev. Side 1

TG86643 — Rev. Side 2

Order multiple 25 tags.



Reusable Dura-Tag

TG86418 — Rev. Side 2

TG86442 — Same Back

TG86454 — Same Back

TG86438 — Same Back

TG86416 — Same Back

TG86417 — Same Back

Economy Polyester

TG86537 — Rev. Side 2

TG86556 — Same Back

TG86574 — Same Back

TG86565 — Same Back

TG86535 — Same Back

TG86536 — Same Back

Cardstock Tags

TG86647 — Rev. Side 2

TG86666 — Same Back

TG86684 — Same Back

TG86675 — Same Back

TG86645 — Same Back

TG86646 — Same Back

Order multiple 25 tags.

EZCODE®

Electrical Safety Labels

"Mr. Ouch" NEMA Safety Labels

Fig. 1




Fig. 2

- NEMA recommends use of "Mr. Ouch" labels on transformers located in public areas
- Meets NEMA and UL standards
- Made of tamper-resistant film to prevent defacing and vandalism
- Permanent pressure-sensitive adhesive makes removal virtually impossible




Fig. 3




Fig. 4

CAT. NO.	LEGEND	FIG.	NEMA LABEL SIZE
WUT-0367	DANGER	1	4 1/2" x 8"
WUT-0366	WARNING	2	4 1/2" x 8"
WUT-0369	DANGER (Bilingual)	3	4 1/2" x 10 3/4"
WUT-0368	WARNING (Bilingual)	4	4 1/2" x 10 3/4"

Order multiple 5 labels.

Magnetic Signs



CAT. NO.	SIGN SIZE
MG66002	5" x 3 1/2"
MG66003	5" x 3 1/2"

Order multiple 10 signs.

CAT. NO.	SIGN SIZE
MG66004	5" x 3 1/2"
MG66005	5" x 3 1/2"

CAT. NO.	SIGN SIZE
MG66006	7" x 5"
MG66007	7" x 5"

CAT. NO.	SIGN SIZE
MG66008	7" x 5"
MG66009	7" x 5"

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289



Self-Sticking Polyester Safety Labels

EZCODE®



CAT. NO.	SIGN SIZE
WJA-1100	2¼" x 9"
WQA-1100	5" x 14"



CAT. NO.	SIGN SIZE
WJA-0076	2¼" x 9"
WQA-0076	5" x 14"



CAT. NO.	SIGN SIZE
WHF-0076	2¼" x 4½"

**2 per Card*



CAT. NO.	SIGN SIZE
LB86871	3½" x 5"



CAT. NO.	SIGN SIZE
LB86860	3½" x 5"



CAT. NO.	SIGN SIZE
LB86235	3½" x 5"



CAT. NO.	SIGN SIZE
LB86234	3½" x 5"



CAT. NO.	SIGN SIZE
LB86877	3½" x 5"



CAT. NO.	SIGN SIZE
LB86861	3½" x 5"



CAT. NO.	SIGN SIZE
LB86204	3½" x 5"



CAT. NO.	SIGN SIZE
LB86245	3½" x 5"



CAT. NO.	SIGN SIZE
LB86248	3½" x 5"



CAT. NO.	SIGN SIZE
LB86250	3½" x 5"



CAT. NO.	SIGN SIZE
LB89413	3½" x 10"
LB89414	5" x 7"

Order multiple 5 cards.

EZCODE®

Safety Signs

Avoid potential catastrophes by clearly marking hazard areas!

Electrical Hazard Safety Signs

AL — Aluminum: 5- to 8-year durability

PL — Plastic: 1- to 2-year durability

SS — Self Sticking: 5- to 8-year durability



CAT NO.	MAT.	SIZE
BP43109	AL	7 x 10
BP43110	AL	10 x 14
BP25532	PL	7 x 10
BP25533	PL	10 x 14
BP84876	SS	7 x 10
BP84877	SS	10 x 14



CAT NO.	MAT.	SIZE
BP40667	AL	7 x 10
BP40668	AL	10 x 14
BP22103	PL	7 x 10
BP22104	PL	10 x 14
BP84083	SS	7 x 10
BP84084	SS	10 x 14



CAT NO.	MAT.	SIZE
BP40997	AL	7 x 10
BP40998	AL	10 x 14
BP22433	PL	7 x 10
BP22434	PL	10 x 14
BP84571	SS	7 x 10
BP84572	SS	10 x 14



CAT NO.	MAT.	SIZE
BP43477	AL	10 x 14
BP25900	PL	10 x 14



CAT NO.	MAT.	SIZE
BP42584	AL	7 x 10
BP42585	AL	10 x 14
BP23061	PL	7 x 10
BP23062	PL	10 x 14
BP88217	SS	7 x 10
BP88218	SS	10 x 14

NEC® compliant signs warn of arc fault danger.

Vinyl Pressure-Sensitive Accident Prevention Signs

New 2002 National Electrical Code Requirement: 110.16 Flash Protection

The new requirement is intended to reduce the occurrence of serious injury or death due to arcing faults to workers who work on or near energized electrical equipment. The warning label should remind a qualified worker who intends to open the equipment for analysis or work that a serious hazard exists and that the worker should follow appropriate work practices and wear appropriate personal protection equipment (PPE) for the specific hazard.



CAT. NO.	LEGEND	COLOR	SIZE
LB94915	WARNING ARC FLASH AND SHOCK	Orange and black on white	7" x 10"
LB94916	WARNING ARC FLASH AND SHOCK	Orange and black on white	10" x 14"

Order by cards. 5 identical cards per standard package poly bag.

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

Custom Sign Express Order Form

This Custom Sign Order Form is for the convenience of you and your authorized Thomas & Betts Distributor. To help expedite your order, please copy the order form and use a separate form to order signs that require different legends, different sizes, different headers, or different materials.

Fax your order to: 901-252-1321

Materials and Available Sizes:

Please check appropriate box for material and size.


Material	Available Sizes					
☐ Aluminum	☐ 7 x 10	☐ 10 x 14				
☐ Plastic	☐ 7 x 10	☐ 10 x 14				
☐ Self-Sticking	☐ 3 x 5	☐ 5 x 7	☐ 7 x 10	☐ 9 x 12	☐ 10 x 14	

Quantity:

No minimum order. Orders for 50+ signs are welcome. Call for delivery and additional volume discounts.

Header/Color:

Please check one of the options below for Spanish or English language.

☐ 	☐ 	☐ 	☐ 	☐ 
☐ 	☐ 	☐ 	☐ 	☐ 
☐ Red & Black Header on White	☐ Blue Header on White	☐ Black Header on Yellow	☐ Green Header on White	☐ Black Header on Orange
☐ 	☐ Black on White	☐ Black on Yellow	☐ Red on White	☐ Magenta on Yellow
	☐ Black on Orange	☐ Green on White	☐ Blue on White	

Legend:

Please print your message clearly in the box below

☐ Lay out best way ☐ Lay out exactly as shown below

Distributor Billing Location:

Distributor Name: _____

Distributor Address: _____

P.O. Number: _____

Contact Name: _____

Phone Number: _____

Fax Number: _____

Pictograms:

A pictogram can be included on your custom sign, in black, at no additional charge.

Please indicate pictogram number below.

					
1 Ear Protection	2 Eye Protection	3 Head Protection	4 Slip	5 Respirator	6 Confined Space
					
7 Lockout/Tagout	8 Pinch	9 Cut/Sever	10 Electrical	11 Electrical	12 Flammable
					
13 Eye Wash Station	14 Stop	15 No Parking	16 Keep Out	17 No Smoking	18 Fire Extinguisher

Shipping Location:

Your Name/Title: _____

Company Name: _____

Attn: _____

Address: _____

City: _____ State: _____ Zip: _____

Phone/Fax Number: _____

P.O. Number: _____

E-Z-Code

EZCODE®

Tool Services

Count on Thomas & Betts for the Right Tools for the Right Job!

Since the 1930s, Thomas & Betts has been supplying tools, dies and connectors. Today, with more than 75 years experience in tools, dies and connectors, Thomas & Betts still sets the standard for innovation, quality and performance for application tooling. Rely on Thomas & Betts tools for labor-saving features, user comfort and convenience, long service life and extraordinary value.

Application Tooling Support — At Your Service

For more than 40 years, Thomas & Betts' highly trained, experienced and dedicated Tool Services staff has been supporting customers in every aspect of their tooling needs. With 100-plus years of combined experience, T&B application tool specialists are ready to assist you with:

- Tool recommendations based on your application and workload
- Demonstrations
- Rental and leasing programs
- On-site installation
- On-site training
- Technical support
- Calibration and certification (factory or on-site)
- Repair (both warranty and non-warranty)
- Loaners for temporary use during repairs
- Supplying components and technical documentation for customer-performed repairs

Tool Repair

Thomas & Betts Tool Services repairs all Thomas & Betts tools, from simple hand tools to hydraulic pumps and crimping heads. Tool Services performs all warranty repairs and can supply you with a temporary loaner tool when necessary. Tool Services can also perform non-warranty repairs, or, if you wish to repair your own tools, contact Tool Services to obtain any needed components, technical documentation and support.

Tool Rental Program

For short-term installation projects, sometimes it makes more sense to rent than buy power tools. Thomas & Betts Tool Services understands this and has created a Tool Rental Program, geared specifically for contractors and projects, to meet the need. Renting T&B tools is easy. A rental agreement is available on our web site, and you can pay the rental fee by credit card. Call Tool Services at **1-800-284-TOOL (8665)** for more details, including a list of Thomas & Betts tools available for rental.



Tool Leasing Program

For longer term use, many OEMs find that leasing high-end tools may be more financially attractive than purchasing. Call Tool Services at **1-800-284-TOOL (8665)** for more information and a list of Thomas & Betts tools available for lease.

Thomas & Betts Tool Warranty

You can choose Thomas & Betts tools with confidence, because we stand behind them with our warranty. The chart below shows the standard length of warranty for different types of tools. See below for additional warranty details.

1 Year

- Cable Tie Installation Tools
- Printers
- Cable Cutters & Strippers
- Dies

2 Years

- Mechanical Hand Tools with Shure-Stake® Mechanism
- Pneumatic Tools
- Hydraulic Pumps
- Battery-Operated Tools

5 Years

- Mechanical Hand Tools without Shure-Stake® Mechanism
- Hydraulic Tools (self-contained and remote heads)

Call Toll-Free 1-800-284-TOOL (8665)

For more information about Thomas & Betts Tool Services:

E-Mail us at toolservice@tnb.com

Limited Warranty for Tools

Thomas & Betts sells tools with the understanding that the user will perform all necessary tests to determine the suitability of each tool for the user's intended application. Thomas & Betts warrants that its tools will be free from defects in materials and workmanship for the period of time specified above. Upon prompt notification of any warranted defect, Thomas & Betts will, at its option, repair or replace the defective product or refund the purchase price. Proof of purchase is required. Misuse or unauthorized modification of the product voids all warranties.

Limitations and Exclusions

The warranty above is the sole warranty concerning this product, and is in lieu of all other warranties express or implied, including but not limited to any implied warranty of merchantability or fitness for a particular purpose, which are specifically disclaimed. Liability for breach of the above warranty is limited to cost of repair or replacement of the product, and under no circumstances will Thomas & Betts be liable for any indirect, special, incidental or consequential damages.

Direct all warranty inquiries to: Thomas & Betts Tool Services **1-800-284-TOOL (8665)**.

Thomas & Betts

www.tnb.com

United States

Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services

Tel: 888.862.3289