



## Identification

## Part No.


## Drawing

## Dimensions in mm


**Hybrid fibre optic cable,  
multi mode, double ended  
2 x G50/125 + 3 x 2.5 mm<sup>2</sup>**

|                 |                          |                                          |
|-----------------|--------------------------|------------------------------------------|
| Length: a = 1 m | AC version<br>DC version | 33 57 211 0015 001<br>33 57 211 0015 002 |
| a = 5 m         | AC version<br>DC version | 33 57 211 0055 001<br>33 57 211 0055 002 |
| a = 10 m        | AC version<br>DC version | 33 57 211 0105 001<br>33 57 211 0105 002 |
| a = 20 m        | AC version<br>DC version | 33 57 211 0205 001<br>33 57 211 0205 002 |
| a = 40 m        | AC version<br>DC version | 33 57 211 0405 001<br>33 57 211 0405 002 |
| a = 50 m        | AC version<br>DC version | 33 57 211 0505 001<br>33 57 211 0505 002 |
| a = 100 m       | AC version<br>DC version | 33 57 211 1005 001<br>33 57 211 1005 002 |

## double ended



a = length




Protection level: IP 65 / IP 67

**Hybrid fibre optic cable,  
multi mode, single ended  
2 x G50/125 + 3 x 2.5 mm<sup>2</sup>**

|                 |                          |                                          |
|-----------------|--------------------------|------------------------------------------|
| Length: a = 1 m | AC version<br>DC version | 33 57 111 0015 001<br>33 57 111 0015 002 |
| a = 5 m         | AC version<br>DC version | 33 57 111 0055 001<br>33 57 111 0055 002 |
| a = 10 m        | AC version<br>DC version | 33 57 111 0105 001<br>33 57 111 0105 002 |
| a = 20 m        | AC version<br>DC version | 33 57 111 0205 001<br>33 57 111 0205 002 |
| a = 40 m        | AC version<br>DC version | 33 57 111 0405 001<br>33 57 111 0405 002 |
| a = 50 m        | AC version<br>DC version | 33 57 111 0505 001<br>33 57 111 0505 002 |
| a = 100 m       | AC version<br>DC version | 33 57 111 1005 001<br>33 57 111 1005 002 |

## single ended



a = length

**Hybrid fibre optic cable,  
multi mode, 50 µm**

|               |                    |
|---------------|--------------------|
| Length: 10 m  | 33 57 851 0100 002 |
| Length: 20 m  | 33 57 851 0200 002 |
| Length: 500 m | 33 57 851 5000 002 |



PVC jacket

2 x G50/125 + 3 x 2.5 mm<sup>2</sup>

Outer diameter: 12.6 mm

Min. bending radius:

single: 5 x OD

repeated: 10 x OD