

Marker cards - SK 6,2/3,8:UNBEDRUCKT - 0805425

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker cards, Card, white, Unlabeled, Can be labeled with: Thermomark R, Thermomark X, Thermomark S, Mounting type: Adhesive, For terminal block width: 6.2 mm

The illustration shows version
SK 6,2/3,8 CONSEC.NOS

Key commercial data

Packing unit	0
Minimum order quantity	10
Catalog page	Page 503 (CL-2009)
GTIN	 4 017918 129163
Custom tariff number	39199000
Country of origin	GERMANY

Technical data

General

Note	Can be labeled with CMS
Height	3.8 mm
Color	white
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C
Components	free from silicone and halogen
Material	Polyester

Classifications

eclass

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27149103
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

Marker cards - SK 6,2/3,8:UNBEDRUCKT - 0805425

Classifications

etim

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Marking

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black