


LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
			A4	REVISED PER ECR-13-017674	12DEC2013	GRZ JL



- 1 CONTINUOUS STRIP ON REELS.
- 2 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 3 WIRE RANGE: 14000 – 22000 CMA.
- 4 CRIMP WIDTH: .250 F TYPE, CURVED ANVIL
CRIMP HEIGHT (±.003)=(TOTAL CMA+36,500)/421,000
CRIMP WIDTH: .250 F TYPE, FLAT ANVIL
CRIMP HEIGHT (±.003)=(TOTAL CMA+32,700)/421,000
CRIMP WIDTH: .270 F TYPE, CURVED OR FLAT ANVIL
CRIMP HEIGHT (±.003)=(TOTAL CMA+34,500)/470,600
GENERAL APPLICATION GUIDELINES MUST BE FOLLOWED AS SPECIFIED IN CATALOG #82221
FOR APPLICATOR INFORMATION CALL:1-800-722-1111
FOR PRODUCT INFORMATION CALL:1-800-522-6752

SECTION A—A
SCALE 20:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
REF 0.76±0.05
[.030±.002] BRASS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± 0.38 [.015]
4 PLC ± —
ANGLES ± 1° 0'

FINISH
TIN PLATE

DWN JR RUTH 02MAY11
CHK KURT RANDOLPH 02MAY11
APVD KURT RANDOLPH 02MAY11

PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT —

TE Connectivity

SPLICE, AMPLIVAR

SIZE A3 CAGE CODE 00779 DRAWING NO C-1742898

CUSTOMER DRAWING

1742898-1

PART NO

RESTRICTED TO —

SCALE 6:1 SHEET 1 OF 1 REV A4

1470-19 (3/11)