





Dimensions: mm (In.)



Mouser Stock No.	Position	Dimension "A" (In.)
106-1222	2	.198
106-1224	4	.398
106-1228	8	.881

Electrical Specifications:

- Electrical life: 2,000 operations min.
- Rating: Non-switching: 50VDC / 100mA,
Switching rating: 50mA / 24VDC
- Contact resistance: 30mΩ max. initial
100mΩ max. @ end of life
- Insulation resistance: 100M min. @ end of life
- Dielectric strength: 500VDC for 1 minute
- Capacitance: 5pF max. between adjacent closed switch.
- Frequency: 1MHz

Mechanical Specifications:

- Type: SPST
- Mechanical life: 5,000 operations min.
- Operation force: <800g
- Stroke: 1.0mm
- Operation & storage temperature: -40°C~ +85°C

Ultra-Low Profile DIP Switches
106-1222, 106-1224, 106-1228

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[106-1228](#)