



## FINISH - PLATING OPTIONS:

1155-05-XXXX

| FINISH CODE | COMPONENT         | FINISH             | FINISH AND SPECIFICATION                                                                                |
|-------------|-------------------|--------------------|---------------------------------------------------------------------------------------------------------|
| 01          | TERMINAL          | SILVER             | 0.000300"MIN. SILVER PER ASTM B700, TYPE 2, GRADE D WITH A NON-CHROMATE PRESERVATIVE TREATMENT          |
|             | BASE/METAL SLEEVE | N/A                | N/A                                                                                                     |
|             | NUT               | N/A                | N/A                                                                                                     |
|             | WASHER            | N/A                | N/A                                                                                                     |
| 03          | TERMINAL          | GOLD               | 0.000010"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290        |
|             | BASE/METAL SLEEVE | N/A                | N/A                                                                                                     |
|             | NUT               | N/A                | N/A                                                                                                     |
|             | WASHER            | N/A                | N/A                                                                                                     |
| 04          | TERMINAL          | ELECTRO-TIN        | 0.000300"MIN. ELECTRO-TIN PER ASTM B545 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290                  |
|             | BASE/METAL SLEEVE | N/A                | N/A                                                                                                     |
|             | NUT               | N/A                | N/A                                                                                                     |
|             | WASHER            | N/A                | N/A                                                                                                     |
| 044         | TERMINAL          | BRIGHT ELECTRO-TIN | 0.000300"MIN. BRIGHT ELECTRO-TIN PER ASTM B545 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290           |
|             | BASE/METAL SLEEVE | N/A                | N/A                                                                                                     |
|             | NUT               | N/A                | N/A                                                                                                     |
|             | WASHER            | N/A                | N/A                                                                                                     |
| 05          | TERMINAL          | ELECTRO-SOLDER     | 0.000300"MIN. ELECTRO-SOLDER PER SAE-AMS-P-81728 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290         |
|             | BASE/METAL SLEEVE | N/A                | N/A                                                                                                     |
|             | NUT               | N/A                | N/A                                                                                                     |
|             | WASHER            | N/A                | N/A                                                                                                     |
| 088         | TERMINAL          | BRIGHT TIN-LEAD    | 0.000300"MIN. BRIGHT TIN-LEAD (Sn93%-Pb7%) PER ASTM B545 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290 |
|             | BASE/METAL SLEEVE | N/A                | N/A                                                                                                     |
|             | NUT               | N/A                | N/A                                                                                                     |
|             | WASHER            | N/A                | N/A                                                                                                     |

## INSULATION COLOR OPTIONS:

1155-05-XX **XX**

| INSULATION COLOR | BLACK | BROWN | RED | ORANGE | YELLOW | GREEN | BLUE | VIOLET | GRAY | WHITE |
|------------------|-------|-------|-----|--------|--------|-------|------|--------|------|-------|
| COLOR CODE NO.   | 10    | 11    | 12  | 13     | 14     | 15    | 16   | 17     | 18   | 19    |

## TOLERANCES:\*

| DECIMAL | FRACTIONAL | ANGULAR | DRAWING ORIGATION DATE | LAST MODIFICATION DATE |
|---------|------------|---------|------------------------|------------------------|
| ± 0.005 | ± 1/64     | ± 5 °   | 4/26/1996              | 3/1/2017               |

\*All dimensions are in inches.

## RoHS COMPLIANCE:

## 1155-05-01XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 1155-05-0110 | YES            |
| 1155-05-0111 | NO             |
| 1155-05-0112 | NO             |
| 1155-05-0113 | NO             |
| 1155-05-0114 | NO             |
| 1155-05-0115 | YES            |
| 1155-05-0116 | YES            |
| 1155-05-0117 | YES            |
| 1155-05-0118 | NO             |
| 1155-05-0119 | YES            |

## 1155-05-03XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 1155-05-0310 | YES            |
| 1155-05-0311 | NO             |
| 1155-05-0312 | NO             |
| 1155-05-0313 | NO             |
| 1155-05-0314 | NO             |
| 1155-05-0315 | YES            |
| 1155-05-0316 | YES            |
| 1155-05-0317 | YES            |
| 1155-05-0318 | NO             |
| 1155-05-0319 | YES            |

## 1155-05-04XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 1155-05-0410 | YES            |
| 1155-05-0411 | NO             |
| 1155-05-0412 | NO             |
| 1155-05-0413 | NO             |
| 1155-05-0414 | NO             |
| 1155-05-0415 | YES            |
| 1155-05-0416 | YES            |
| 1155-05-0417 | YES            |
| 1155-05-0418 | NO             |
| 1155-05-0419 | YES            |

## 1155-05-044XX

| PART NUMBER   | RoHS COMPLIANT |
|---------------|----------------|
| 1155-05-04410 | YES            |
| 1155-05-04411 | NO             |
| 1155-05-04412 | NO             |
| 1155-05-04413 | NO             |
| 1155-05-04414 | NO             |
| 1155-05-04415 | YES            |
| 1155-05-04416 | YES            |
| 1155-05-04417 | YES            |
| 1155-05-04418 | NO             |
| 1155-05-04419 | YES            |

## 1155-05-05XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 1155-05-0510 | NO             |
| 1155-05-0511 | NO             |
| 1155-05-0512 | NO             |
| 1155-05-0513 | NO             |
| 1155-05-0514 | NO             |
| 1155-05-0515 | NO             |
| 1155-05-0516 | NO             |
| 1155-05-0517 | NO             |
| 1155-05-0518 | NO             |
| 1155-05-0519 | NO             |

## 1155-05-088XX

| PART NUMBER   | RoHS COMPLIANT |
|---------------|----------------|
| 1155-05-08810 | NO             |
| 1155-05-08811 | NO             |
| 1155-05-08812 | NO             |
| 1155-05-08813 | NO             |
| 1155-05-08814 | NO             |
| 1155-05-08815 | NO             |
| 1155-05-08816 | NO             |
| 1155-05-08817 | NO             |
| 1155-05-08818 | NO             |
| 1155-05-08819 | NO             |

TOOLING:

| INSTALLATION TOOL:<br>ARBOR PRESS | INSTALLATION TOOL:<br>ANVIL<br>(ARBOR PRESS OPERATED) | INSTALLATION TOOL:<br>PRESS-FIT / ROLL SWAGE / RIVET PUNCH<br>(ARBOR PRESS OPERATED) | INSTALLATION TOOL:<br>PRESS-FIT<br>(HAND OPERATED) |
|-----------------------------------|-------------------------------------------------------|--------------------------------------------------------------------------------------|----------------------------------------------------|
| TM1                               | TA1155-05                                             | TPI1155-05                                                                           | TTI1155-05                                         |

NOTES:

| DATASHEET NOTES                                                                                                                                               |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| N/A                                                                                                                                                           |
| INSTRUCTION NOTES                                                                                                                                             |
| SEE GENERAL PRESS FIT INSTALLATION INSTRUCTION ON CONCORD ELECTRONICS' WEBSITE <a href="http://WWW.CONCORD-ELECTRONICS.COM">WWW.CONCORD-ELECTRONICS.COM</a> . |