

F310 HSS Metric Fine Dies



BS1127:1950
Tolerance: 6g
Chamfer lead: 1.5 threads
Cutting rake: 8°
Surface treatment: Bright
Range: 4 - 25mm
Application: For hand or machine production of components less than 3x diameter in length.

494130

Size x Pitch(mm)	Cutter Diameter(in)	Order Code	Price Each
4 x 0.50	1 ³ / ₁₆	020-400	
5 x 0.50	1 ³ / ₁₆	024-748	
6 x 0.75	1 ³ / ₁₆	147-4009	
8 x 1.00	1.000	147-4010	
10 x 0.75	1.000	147-4011	
10 x 1.00	1.000	147-4012	
10 x 1.25	1.000	147-4013	
12 x 1.00	1 ⁵ / ₁₆	147-4014	
12 x 1.25	1 ⁵ / ₁₆	147-4015	
12 x 1.50	1 ⁵ / ₁₆	147-4016	
14 x 1.25	1 ⁵ / ₁₆	147-4018	
14 x 1.50	1 ⁵ / ₁₆	147-4019	
16 x 1.00	1½	220-577B	
16 x 1.50	1 ⁵ / ₁₆	147-7476	
18 x 1.50	1½	147-4020	
25 x 1.50	2.000	147-7494	