




- VDC: 12, 24, 48
- RPM: 1150~2800
- CFM: 47.33~124.18
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 24; UL 1007 lead wires
- Mass:250.5g




## DC FAN 120x120x38mm


### Specification

|           | Bearing                                              | Voltage | Current  | Speed     | Input Power | Air Flow     | Static Pressure       | Noise     | Weight |
|-----------|------------------------------------------------------|---------|----------|-----------|-------------|--------------|-----------------------|-----------|--------|
| MODEL NO  | ○ Sleeve<br>● One ball and one sleeve<br>○ Hydraulic | (Vdc)   | (Amp)    | (Rpm)     | (Watts)     | (CFM)        | (mm/H <sub>2</sub> O) | dB(A)     | Gram   |
| B1238B12E | ●                                                    | 12      | 0.09     | 1150      | 1.08        | 47.33        | 1.33                  | 22.9      | 250.5  |
| B1238B12L | ●                                                    | 12      | 0.26     | 1800      | 3.12        | 76.54        | 3.09                  | 34.4      | 250.5  |
| B1238B12M | ●                                                    | 12      | 0.33     | 2200      | 3.96        | 98.43        | 5.07                  | 38.7      | 250.5  |
| B1238B12H | ●                                                    | 12      | 0.50     | 2600      | 6.00        | 114.79       | 6.79                  | 45.0      | 250.5  |
| B1238B12U | ●                                                    | 12      | 0.65     | 2800      | 7.80        | 124.18       | 8.20                  | 45.4      | 250.5  |
| B1238B24E | ●                                                    | 24      | 0.10     | 1150      | 2.40        | 47.33        | 1.33                  | 22.9      | 250.5  |
| B1238B24L | ●                                                    | 24      | 0.15     | 1800      | 3.60        | 76.54        | 3.09                  | 34.4      | 250.5  |
| B1238B24M | ●                                                    | 24      | 0.25     | 2200      | 6.00        | 98.43        | 5.07                  | 38.7      | 250.5  |
| B1238B24H | ●                                                    | 24      | 0.35     | 2600      | 8.40        | 114.79       | 6.79                  | 45.0      | 250.5  |
| B1238B48L | ●                                                    | 48      | 0.08     | 1800      | 3.84        | 76.54        | 3.09                  | 34.4      | 250.5  |
| B1238B48M | ●                                                    | 48      | 0.15     | 2200      | 7.20        | 98.43        | 5.07                  | 38.7      | 250.5  |
| B1238B48H | ●                                                    | 48      | 0.18     | 2600      | 8.64        | 114.79       | 6.79                  | 45.0      | 250.5  |
| E1238B12H | ●                                                    | 12      | 0.2~0.50 | 1150~2600 | 2.4~6.0     | 47.33~114.79 | 1.33~6.79             | 22.9~45.0 | 250.5  |
| F1238B12E | ●                                                    | 12      | 0.11     | 1150      | 1.32        | 47.33        | 1.33                  | 22.9      | 250.5  |
| F1238B12L | ●                                                    | 12      | 0.26     | 1800      | 3.12        | 76.54        | 3.09                  | 34.4      | 250.5  |
| F1238B12M | ●                                                    | 12      | 0.40     | 2200      | 4.80        | 98.43        | 5.07                  | 38.7      | 250.5  |
| F1238B12H | ●                                                    | 12      | 0.50     | 2600      | 6.00        | 114.79       | 6.79                  | 45.0      | 250.5  |
| F1238B12U | ●                                                    | 12      | 0.80     | 2800      | 9.60        | 124.18       | 8.20                  | 45.4      | 250.5  |
| F1238B24E | ●                                                    | 24      | 0.10     | 1150      | 2.40        | 47.33        | 1.33                  | 22.9      | 250.5  |
| F1238B24L | ●                                                    | 24      | 0.15     | 1800      | 3.60        | 76.54        | 3.09                  | 34.4      | 250.5  |
| F1238B24M | ●                                                    | 24      | 0.25     | 2200      | 6.00        | 98.43        | 5.07                  | 38.7      | 250.5  |
| F1238B24H | ●                                                    | 24      | 0.45     | 2600      | 10.80       | 114.79       | 6.79                  | 45.0      | 250.5  |
| F1238B24U | ●                                                    | 24      | 0.50     | 2800      | 12.00       | 124.18       | 8.20                  | 45.4      | 250.5  |
| F1238B48M | ●                                                    | 48      | 0.15     | 2200      | 7.20        | 98.43        | 5.07                  | 38.7      | 250.5  |
| F1238B48H | ●                                                    | 48      | 0.20     | 2600      | 9.60        | 114.79       | 6.79                  | 45.0      | 250.5  |
| P1238B24H | ●                                                    | 24      | 0.2~0.32 | 1400~2800 | 4.8~7.68    | 65.07~124.18 | 2.32~8.20             | 27.3~45.4 | 250.5  |
| R1238B12H | ●                                                    | 12      | 0.2~0.50 | 1150~2600 | 2.4~6.0     | 47.33~114.79 | 1.33~6.79             | 22.9~45.0 | 250.5  |

Design specifics subject to change without notice.




### STATIC PRESSURE





- VDC: 12
- RPM: 2800
- CFM: 142.37
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 24; UL 1007 lead wires
- Mass: 265.5g




DC FAN 120x120x38mm

Specification

| MODEL NO   | Bearing                                              | Voltage | Current | Speed | Input Power | Air Flow | Static Pressure       | Noise | Weight |
|------------|------------------------------------------------------|---------|---------|-------|-------------|----------|-----------------------|-------|--------|
|            | ○ Sleeve<br>● One ball and one sleeve<br>○ Hydraulic | (Vdc)   | (Amp)   | (Rpm) | (Watts)     | (CFM)    | (mm/H <sub>2</sub> O) | dB(A) | Gram   |
| F1238B12UY | ●                                                    | 12      | 0.85    | 2800  | 10.20       | 142.37   | 8.79                  | 47.4  | 265.5  |

Design specifics subject to change without notice.



STATIC PRESSURE

