

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		P	REVISED PER ECO-14-015277	24FEB2015	NK	DR

 WIRE RANGE	 E13288 Listed	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED

- 1

STAMP "AMP - SEE TABLE" APPROX AS SHOWN.
- 2

WIRE INSULATION DIA: SEE TABLE.
- 3

TONGUE MATERIAL THK: .031±.002.
- 4

BODY: TIN PLATE .000100 MIN EXT THK PER ASTM B545.
- 5

SLEEVE: TIN PLATE .000100 MIN EXT THK PER ASTM B545.
- 6

BODY & SLEEVE- CU PER ASTM B152
INSULATION - NYLON PER ASTM D4066
COLOR - BLUE.
- 7

APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 8

MEETS MS25036-154, CLASS 1 & 2.
- 9

MEETS MS25036-154, CLASS 2.
- 10

MEETS M7928/1-43, CLASS 1 & 2.
- 11

MEETS M7928/1-52, CLASS 1 & 2.