



JKL PART NUMBER	LENGTH A +/- 2mm	COLOR (REF.)	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF5118-20B	118mm	RGB HIGH OUTPUT WHITE 5400° KELVIN	600	305	5 ± 1	7000 ± 700	20,000
BF5165-20B	165mm		800	400	5 ± 1	7000 ± 700	20,000
BF5200-20B	200mm		850	445	5 ± 1	7000 ± 700	20,000
BF5300-20B	300mm		1000	600	5 ± 1	7000 ± 700	20,000

*NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE SINGLE LEAD TIPLESS MINIATURE FLUORESCENT LAMP				
A	6.3 TO 6.2 MAX., ADD 5.0 DIM.	2/29/00	DRAWN BY	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.			
	RELEASED - CANCEL BF-5mm DIA DRAWING	2/25/00	L. WENGSTROM	JK	02/29/00	A	55335	BF 5-20B			
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	- CAD DRAWING -			SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET	
			MANUAL REVISIONS NOT PERMITTED			NONE	2/25/00	2/29/00	A	1 OF 1	