



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™



ROPE-9/16 X 300' NYLON/POLYESTER

Double-Braided Composite Rope 9/16 × 300' (14.3 mm × 91 m)

Cat No: 35283

UPC No: 783310352839

Description

- Double-braided inner core with an extra double-braided outer jacket for added strength and less stretch
- white with green tracer
- Rot and mildew resistant
- Factory spliced eyes at both ends
- Lowest stretch
- Select a rope with a maximum rated capacity that meets or exceeds the cable puller's maximum pulling force

Specifications

- Application : For The UT4 And 640 Puller
- Average Breaking Strength : 16000.000 LB (71.100 KN)
- Color : White With Green Tracer
- Material : Nylon/Polyester
- Maximum Rated Capacity : 4000.000 LB (17.800 KN)
- Rope Diameter : 9/16 IN (14.300 MM)
- Rope Length : 300.000 FT (91.000 M)
- Rope Stand : 644
- Type : Double Braided
- Weight : 28.000 LB (12.700 KG)