

## LIGHTED TOGGLES



Fig. 1



Fig. 2



Fig. 3



Fig. 4

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | AMPS 12 VDC | Actuator Style | Lamp Color        | Terminal Type  | Bushing Length | Mounting Hole | Hardware | Spec. Drawing Page/Part No. |
|-----------------|---------------|------------|------------------|--------------|-------------|----------------|-------------------|----------------|----------------|---------------|----------|-----------------------------|
| 35-3300         | 35-3300-BU    | 1          | On Off           | SPST         | 20          | LED Tip        | Lighted Red LED   | QC .250"       | 0.400"         | 0.500"        | KN       | 279-A                       |
| 35-3301         | 35-3301-BU    | 1          | On Off           | SPST         | 20          | LED Tip        | Lighted Green LED | QC .250"       | 0.400"         | 0.500"        | KN       | 279-A                       |
| 35-3302         | 35-3302-BU    | 1          | On Off           | SPST         | 20          | LED Tip        | Lighted Amber LED | QC .250"       | 0.400"         | 0.500"        | KN       | 279-A                       |
| 35-3303         | 35-3303-BU    | 1          | On Off           | SPST         | 20          | LED Tip        | Lighted Blue LED  | QC .250"       | 0.400"         | 0.500"        | KN       | 279-A                       |
| 35-3310         | 35-3310-BU    | 2          | On Off           | SPST         | 20          | LED Duckbill   | Lighted Red LED   | QC .250"       | 0.400"         | 0.500"        | KN       | 279-B                       |
| 35-3311         | 35-3311-BU    | 2          | On Off           | SPST         | 20          | LED Duckbill   | Lighted Green LED | QC .250"       | 0.400"         | 0.500"        | KN       | 279-B                       |
| 35-3312         | 35-3312-BU    | 2          | On Off           | SPST         | 20          | LED Duckbill   | Lighted Amber LED | QC .250"       | 0.400"         | 0.500"        | KN       | 279-B                       |
| 35-3313         | 35-3313-BU    | 2          | On Off           | SPST         | 20          | LED Duckbill   | Lighted Blue LED  | QC .250"       | 0.400"         | 0.500"        | KN       | 279-B                       |
| 35-3320         | 35-3320-BU    | 3          | On Off           | SPST         | 20          | LED Paddle     | Lighted Red LED   | QC .250"       | N/A            | 0.944"        | N/A      | 279-C                       |
| 35-3321         | 35-3321-BU    | 3          | On Off           | SPST         | 20          | LED Paddle     | Lighted Green LED | QC .250"       | N/A            | 0.944"        | N/A      | 279-C                       |
| 35-3322         | 35-3322-BU    | 3          | On Off           | SPST         | 20          | LED Paddle     | Lighted Amber LED | QC .250"       | N/A            | 0.944"        | N/A      | 279-C                       |
| 35-3323         | 35-3323-BU    | 3          | On Off           | SPST         | 20          | LED Paddle     | Lighted Blue LED  | QC .250"       | N/A            | 0.944"        | N/A      | 279-C                       |
| 35-3330         | 35-3330-BU    | 4          | On Off           | SPST         | 20          | LED Tip        | Lighted Red LED   | QC.187"/Solder | N/A            | 0.866"        | N/A      | 279-D                       |
| 35-3331         | 35-3331-BU    | 4          | On Off           | SPST         | 20          | LED Tip        | Lighted Green LED | QC.187"/Solder | N/A            | 0.866"        | N/A      | 279-D                       |
| 35-3332         | 35-3332-BU    | 4          | On Off           | SPST         | 20          | LED Tip        | Lighted Amber LED | QC.187"/Solder | N/A            | 0.866"        | N/A      | 279-D                       |
| 35-3333         | 35-3333-BU    | 4          | On Off           | SPST         | 20          | LED Tip        | Lighted Blue LED  | QC.187"/Solder | N/A            | 0.866"        | N/A      | 279-D                       |

Note: All figures are for illustration purpose only, and the number/type of terminals may vary  
 QC=Quick Connect  
 KN=Knurled Nut








Fig. 5

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | AMPS 12 VDC | Actuator Style  | Lamp Color        | Terminal Type | Bushing Length | Mounting Hole | Hardware | Spec. Drawing Page/Part No. |
|-----------------|---------------|------------|------------------|--------------|-------------|-----------------|-------------------|---------------|----------------|---------------|----------|-----------------------------|
| 35-3370         | 35-3370-BU    | 5          | On Off           | SPST         | 30          | LED Oval Rocker | Lighted Red LED   | QC .250"      | 0.350"         | 0.500"        | KN       | 279-E                       |
| 35-3371         | 35-3371-BU    | 5          | On Off           | SPST         | 30          | LED Oval Rocker | Lighted Green LED | QC .250"      | 0.350"         | 0.500"        | KN       | 279-E                       |
| 35-3372         | 35-3372-BU    | 5          | On Off           | SPST         | 30          | LED Oval Rocker | Lighted Amber LED | QC .250"      | 0.350"         | 0.500"        | KN       | 279-E                       |
| 35-3373         | 35-3373-BU    | 5          | On Off           | SPST         | 30          | LED Oval Rocker | Lighted Blue LED  | QC .250"      | 0.350"         | 0.500"        | KN       | 279-E                       |

Note: All figures are for illustration purpose only, and the number/type of terminals may vary  
 QC=Quick Connect  
 KN=Knurled Nut

## LIGHTED TOGGLES (Cont.)



## LIGHTED MINIATURE ROCKERS




Fig. 1




Fig. 2

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | AMPS 125VAC | AMPS 250VAC | Actuator Color     | Terminal Type   | Mounting Hole | Spec. Drawing Page/Part No. |
|-----------------|---------------|------------|------------------|--------------|-------------|-------------|--------------------|-----------------|---------------|-----------------------------|
| 35-680          | 35-680-BU     | 1          | On Off           | SPST         | 5           | 3           | Lighted Orange LED | QC .187"/Solder | 0.512 x 0.750 | 281-A                       |
| 35-681          | 35-681-BU     | 1          | On Off           | SPST         | 5           | 3           | Lighted Green LED  | QC .187"/Solder | 0.512 x 0.750 | 281-A                       |
| 35-682          | 35-682-BU     | 1          | On Off           | SPST         | 5           | 3           | Lighted Red LED    | QC .187"/Solder | 0.512 x 0.750 | 281-A                       |
| 35-645          | 35-645-BU     | 2          | On Off           | SPST         | 10          | 5           | Lighted Red LED    | Solder Eyelet   | 0.755 x 0.508 | 281-B                       |
| 35-646          | 35-646-BU     | 2          | On Off           | DPST         | 10          | 5           | Lighted Red LED    | Solder Eyelet   | 0.755 x 0.508 | 281-B                       |

Notes: (On)/(Off)=Momentary On/Off

QC=Quick Connect

(In Series) Resistor Chart for DC usage (LED). Diode for AC usage except 35-645 and 35-646

| Forward V <sub>FD</sub> | Current I <sub>LED</sub> | Reverse V <sub>R</sub> | Intensity M <sub>CD</sub> | Recommended Resistor @ Voltage |     |      |
|-------------------------|--------------------------|------------------------|---------------------------|--------------------------------|-----|------|
|                         |                          |                        |                           | 5V                             | 12V | 24V  |
| 2.1                     | 10                       | 4V                     | 1.6 typ.                  | 270                            | 1K  | 2.2K |

For 35-645 and 35-646

## MINIATURE ROCKERS




Fig. 3



Fig. 4



Fig. 5




Fig. 6




Fig. 7




Fig. 8




Fig. 9



Fig. 10

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | Amps 125 VAC | Amps 250 VAC | Actuator Color       | Terminal Type | Imprinting Color and Marking | Mounting Hole | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|--------------|--------------|--------------|----------------------|---------------|------------------------------|---------------|------------------------|
| 35-602          | 35-602-BU     | 3          | On On            | SPDT         | 4            | 2            | Black Plastic        | Solder Lug    |                              | 0.350 x 0.734 | 281-C                  |
| 35-603          | 35-603-BU     | 3          | On (On)          | SPDT         | 4            | 2            | Black Plastic        | Solder Lug    |                              | 0.350 x 0.734 | 281-C                  |
| 35-604          | 35-604-BU     | 3          | On Off On        | SPDT         | 4            | 2            | Black Plastic        | Solder Lug    |                              | 0.350 x 0.734 | 281-C                  |
| 35-615          | 35-615-BU     | 4          | On On            | SPDT         | 4            | 2            | Black                | QC .187"      |                              | 0.508 x 0.756 | 281-D                  |
| 35-605          | 35-605-BU     | 5          | On Off           | SPST         | 8            | 4            | Black/Red Indicating | QC .187"      | Red O-                       | 0.508 x 0.756 | 281-E                  |
| 35-606          | 35-606-BU     | 6          | On On            | DPDT         | 8            | 4            | Black                | QC .187"      |                              | 0.508 x 0.756 | 281-E                  |
| 35-608          | 35-608-BU     | 6          | On Off           | DPST         | 8            | 4            | Black                | QC .187"      |                              | 0.508 x 0.756 | 281-E                  |
| 35-609          | 35-609-BU     | 6          | On On            | SPDT         | 8            | 4            | Black                | QC .187"      |                              | 0.508 x 0.756 | 281-E                  |
| 35-674          | 35-674-BU     | 7          | On On            | DPDT         | 8            | 4            | Red Plastic          | Solder Lug    |                              | 0.625 x 0.523 | 281-F                  |
| 35-676          | 35-676-BU     | 7          | On Off On        | DPDT         | 8            | 4            | Red Plastic          | Solder Lug    |                              | 0.625 x 0.523 | 281-F                  |
| 35-642          | 35-642-BU     | 8          | On Off           | SPST         | 10           | 6            | Black Plastic        | QC .250"      | White O-                     | 0.508 x 0.755 | 281-G                  |
| 35-644          | 35-644-BU     | 4          | On On            | SPDT         | 10           | 5            | Black                | QC .187"      |                              | 0.508 x 0.756 | 281-D                  |
| 35-648          | 35-648-BU     | 9          | On On            | DPDT         | 10           | 5            | Black                | QC .187"      |                              | 0.887 x 0.756 | 281-D                  |
| 35-607          | 35-607-BU     | 6          | On Off           | SPST         | 11           | N/R          | Black                | QC .187"      |                              | 0.508 x 0.756 | 281-E                  |
| 35-643          | 35-643-BU     | 10         | On Off           | DPST         | 16*          | 16           | Black Plastic        | QC .250"      | White O-                     | 0.483 x 1.021 | 281-H                  |
| 35-3705         |               | 10         | On Off           | DPST         | 16           | 16           | White Plastic        | QC .250"      | Black O-                     | 0.483 x 1.021 | 281-H                  |

Notes: (On)=Momentary On



\*1/4 HP @ 125VAC, 1/2 HP @250VAC

N/R= Not Rated







QC=Quick Connect

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

## LIGHTED MINIATURE ROCKERS (Cont.)



## MINIATURE ROCKERS (Cont.)



## STANDARD APPLIANCE ROCKERS



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7




Fig. 8

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/Throws | AMPS 125VAC | AMPS 250VAC | Actuator Color | Actuator Material | Imprinting Color and Marking | Mounting Hole | Spec. Drawing Page No. |
|-----------------|---------------|----------|------------------|--------------|-------------|-------------|----------------|-------------------|------------------------------|---------------|------------------------|
| 35-3760         | 35-3760-BU    | 1        | (On) Off         | SPST         | 15*         | 10          | White          | Nylon             |                              | 0.550 x 1.125 | 283-A                  |
| 35-691          | 35-691-BU     | 2        | On Off           | SPST         | 16          | 10          | Black          | Nylon             |                              | 0.550 x 1.125 | 283-B                  |
| 35-693          | 35-693-BU     | 3        | On Off           | SPST         | 16          | 10          | Black          | Nylon             | Red On/Off                   | 0.550 x 1.125 | 283-B                  |
| 35-694          | 35-694-BU     | 2        | On Off On        | SPDT         | 16          | 10          | Black          | Nylon             |                              | 0.550 x 1.125 | 283-B                  |
| 35-3030         | 35-3030-BU    | 3        | On Off           | SPST         | 16          | 10          | Black          | Nylon             | Red On/Off                   | 0.550 x 1.125 | 283-B                  |

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/Throws | AMPS 125VAC | AMPS 250VAC | HP 125/250VAC | Actuator Material | Imprinting Color and Marking | Mounting Hole | Spec. Drawing Page No. |
|-----------------|---------------|----------|------------------|--------------|-------------|-------------|---------------|-------------------|------------------------------|---------------|------------------------|
| 35-3600         | 35-3600-BU    | 4        | On Off           | SPST         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3610         | 35-3610-BU    | 4        | On On            | SPDT         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3620         | 35-3620-BU    | 4        | On Off On        | SPDT         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3630         | 35-3630-BU    | 4        | On Off           | DPST         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3636         | 35-3636-BU    | 4        | On Off           | SPST         | 20          | †           | 1-1/2         | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3640         | 35-3640-BU    | 4        | On On            | DPDT         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3650         | 35-3650-BU    | 4        | On Off On        | DPDT         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3660         | 35-3660-BU    | 4        | (On) Off         | DPST         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3670         | 35-3670-BU    | 4        | (Off) On         | DPST         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3680         | 35-3680-BU    | 4        | (On) On          | DPDT         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3690         | 35-3690-BU    | 4        | (On) Off On      | DPDT         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3695         | 35-3695-BU    | 4        | (On) Off (On)    | DPDT         | 15          | 10          | 3/4           | Black Nylon       |                              | 0.830 x 1.450 | 283-D                  |
| 35-3710         | 35-3710-BU    | 4        | On Off           | SPST         | 16          | 10          | 3/4           | Black Nylon       |                              | 0.550 x 1.125 | 283-C                  |
| 35-3720         | 35-3720-BU    | 4        | On On            | SPDT         | 16          | 10          | 3/4           | Black Nylon       |                              | 0.550 x 1.125 | 283-C                  |

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/Throws | AMPS 125VAC | AMPS 250VAC | HP 250 VAC | Actuator Material | Imprinting Color and Marking | Mounting Hole | Spec. Drawing Page No. |
|-----------------|---------------|----------|------------------|--------------|-------------|-------------|------------|-------------------|------------------------------|---------------|------------------------|
| 35-620          | 35-620-BU     | 5        | On Off           | DPST         | 15          | 10          | 1/4        | Red Poly          | White On/Off                 | 0.866 x 1.102 | 283-E                  |
| 35-640          | 35-640-BU     | 6        | On On            | SPDT         | 16          | 16          | 1          | Black Nylon       |                              | 1.100 x 0.453 | 283-F                  |
| 35-695          | 35-695-BU     | 7        | (On) Off (On)    | SPDT         | 16          | 16          | 1          | Black Plastic     |                              | 0.550 x 1.180 | 283-F                  |
| 35-654          | 35-654-BU     | 8        | On Off           | DPST         | 20          | 15          | N/R        | Black Plastic     |                              | 1.000 x 1.125 | 283-G                  |








Notes: (On)=Momentary On  
\*3/4 H.P. @ 125/250VAC

N/R= Not Rated  
All of the Above have Quick Connect .250" Terminals

†=20A @ 277VAC and 2 H.P. @ 250VAC

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

## STANDARD APPLIANCE ROCKERS (Cont.)





## LIGHTED APPLIANCE ROCKERS




Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5




Fig. 6




Fig. 7



Fig. 8



Fig. 9



Fig. 10

### On-Off Circuit Function

| Retail Part No. | Bulk Part No. | Fig. No. | Poles/Throws | Amps 125 VAC | Amps 250 VAC | HP 125 VAC | HP 250 VAC | HP 125-250 VAC | Actuator Color        | Actuator Material | Lamp Voltage | Mounting Hole | Spec. Drawing Page/Part No. |
|-----------------|---------------|----------|--------------|--------------|--------------|------------|------------|----------------|-----------------------|-------------------|--------------|---------------|-----------------------------|
| 35-660          | 35-660-BU     | 1        | SPST         | **           | N/R          |            |            |                | Lighted Red           |                   | 12V Incdt    | 0.550 x 1.125 | 285-A                       |
| 35-684          | 35-684-BU     | 2        | SPST         | 10           | N/R          | N/R        | N/R        | N/R            | White w/ Red LED      | Plastic           | ***          | 0.430 x 1.189 | 285-B                       |
| 35-696          | 35-696-BU     | 3        | SPST         | 12           | 8            |            |            | 1/2            | Lighted Red           | Nylon             | 125V Ne      | 0.508 x 0.756 | 285-C                       |
| 35-656          | 35-656-BU     | 4        | SPST         | 15           | 10           |            |            | 1/2            | Black w/Lighted Amber | Nylon             | 125V Ne      | 1.450 x 0.830 | 285-D                       |
| 35-662          | 35-662-BU     | 5        | SPST         | 15           | 15           | 1/2        | 1          |                | Lighted Amber         | Nylon             | 12V Incdt    | 0.453 x 1.110 | 285-E                       |
| 35-664          | 35-664-BU     | 5        | SPST         | 15           | 15           | 1/2        | 1          |                | Lighted Green         | Nylon             | 12V Incdt    | 0.453 x 1.110 | 285-E                       |
| 35-688          | 35-688-BU     | 5        | SPST         | 15           | 15           | 1/2        | 1          |                | Lighted Red           | Nylon             | 125V Ne      | 0.453 x 1.110 | 285-E                       |
| 35-689          | 35-689-BU     | 6        | SPST         | 15*          | 10           |            |            | 3/4            | Lighted Red           | Nylon             | 125V Ne      | 0.550 x 1.125 | 285-F                       |
| 35-3790         | 35-3790-BU    | 6        | SPST         | 15           | 10           |            |            | 3/4            | Lighted Amber         | Nylon             | 125V Ne      | 0.550 x 1.125 | 285-F                       |
| 35-621          | 35-621-BU     | 7        | SPST         | 16           | 16           |            |            |                | Black w/Red Lens      | Plastic           | 125V Ne      | 0.870 x 1.070 | 285-G                       |
| 35-3730         | 35-3730-BU    | 8        | SPST         | 16           | 10           |            |            |                | Lighted Amber         |                   | 125V Ne      | 0.550 x 1.125 | 285-H                       |
| 35-3740         | 35-3740-BU    | 8        | SPST         | 16           | 10           |            |            |                | Lighted Red           |                   | 125V Ne      | 0.550 x 1.125 | 285-H                       |
| 35-655          | 35-655-BU     | 9        | DPST         | 20           | 15           | N/R        | N/R        |                | Lighted Red           | Plastic           | 125V Ne      | 1.000 x 1.125 | 285-I                       |
| 35-686          | 35-686-BU     | 10       | DPST         | 20           | 20           | 1/2        | 1          |                | Black w/Red Indicator | Plastic           | 125V Ne      | 1.180 x 0.870 | 285-J                       |
| 35-3755         | 35-3755-BU    | 8        | SPST         | 15           |              |            |            |                | Red w/ White Dot      |                   | 110V Ne      |               |                             |

Notes: \*Built-in Resistor

\*\*Rated 10 Amps @ 30VDC

\*\*\*Requires external resistor and diode for AC applications (not included)

Incdt=Incandescent

Ne=Neon











N/R=Not Rated

QC=Quick Connect

The Terminal Types for the above parts are QC .250" except for 35-684 is Solder and 35-696 is QC .187".

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

## LIGHTED APPLIANCE ROCKERS (Cont.)





## AUTOMOTIVE/MARINE ROCKERS



Fig. 1



Fig. 2

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/Throws | Amps 125 VAC | Amps 250 VAC | Amps 12 VDC | HP 125-250 VAC | Lamp Color | Lamp Voltage     | Terminal Type | Mounting Hole | Spec. Drawing Page/Part No. |
|-----------------|---------------|----------|------------------|--------------|--------------|--------------|-------------|----------------|------------|------------------|---------------|---------------|-----------------------------|
| 35-3580         | 35-3580-BU    | 1        | On Off           | SPST         | 15           | 10           | N/R         | 1/2            |            |                  | QC .250"      | 0.830 x 1.450 | 287-A                       |
| 35-3585         | 35-3585-BU    | 1        | On On            | DPDT         |              |              | 20          |                |            |                  | QC .250"      | 0.830 x 1.450 | 287-A                       |
| 35-3590         | 35-3590-BU    | 1        | On Off On        | DPDT         |              |              | 20          |                |            |                  | QC .250"      | 0.830 x 1.450 | 287-A                       |
| 35-3500         | 35-3500-BU    | 2        | On Off           | SPST         |              |              | 20          |                | Amber      | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3505         | 35-3505-BU    | 2        | On Off           | SPST         |              |              | 20          |                | Green      | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3510         | 35-3510-BU    | 2        | On Off           | SPST         |              |              | 20          |                | Red        | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3515         | 35-3515-BU    | 2        | On Off           | SPST         |              |              | 20          |                | Blue       | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3520         | 35-3520-BU    | 2        | On Off On        | DPDT         |              |              | 20          |                | Amber      | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3525         | 35-3525-BU    | 2        | On Off On        | DPDT         |              |              | 20          |                | Green      | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3530         | 35-3530-BU    | 2        | On Off On        | DPDT         |              |              | 20          |                | Red        | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3535         | 35-3535-BU    | 2        | On Off On        | DPDT         |              |              | 20          |                | Blue       | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3540         | 35-3540-BU    | 2        | (On) Off         | SPST         |              |              | 20          |                | Amber      | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3545         | 35-3545-BU    | 2        | (On) Off         | SPST         |              |              | 20          |                | Green      | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3550         | 35-3550-BU    | 2        | (On) Off         | SPST         |              |              | 20          |                | Red        | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3555         | 35-3555-BU    | 2        | (On) Off         | SPST         |              |              | 20          |                | Blue       | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3560         | 35-3560-BU    | 2        | (On) Off (On)    | DPDT         |              |              | 20          |                | Amber      | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3565         | 35-3565-BU    | 2        | (On) Off (On)    | DPDT         |              |              | 20          |                | Green      | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3570         | 35-3570-BU    | 2        | (On) Off (On)    | DPDT         |              |              | 20          |                | Red        | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |
| 35-3575         | 35-3575-BU    | 2        | (On) Off (On)    | DPDT         |              |              | 20          |                | Blue       | 12V Incandescent | QC .250"      | 0.830 x 1.450 | 287-B                       |

Notes: For replacement gasket use part number **999-16543-001**  
(On)=Momentary On  
QC=Quick Connect

All above parts have nylon actuators

## ROUND ROCKERS



Fig. 3



Fig. 4



Fig. 5



Fig. 6





Fig. 7

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/Throws | AMPS 125VAC | AMPS 250VAC | HP 250 VAC | Actuator Color       | Imprinting Color and Marking | Terminal Type | Mounting Hole | Spec. Drawing Page/Part No. |
|-----------------|---------------|----------|------------------|--------------|-------------|-------------|------------|----------------------|------------------------------|---------------|---------------|-----------------------------|
| 35-1300         | 35-1300-BU    | 3        | On Off           | SPST         | 10          | 6           |            | Red (Lighted)*       | White O- (See Fig.)          | QC .187"      | 0.7952"       | 287-C                       |
| 35-1301         | 35-1301-BU    | 3        | On Off           | SPST         | 10          | 6           |            | Green (Lighted)*     | White O- (See Fig.)          | QC .187"      | 0.7952"       | 287-C                       |
| 35-1302         | 35-1302-BU    | 4        | On Off           | SPST         | 10          | 6           |            | Black                | White O- (See Fig.)          | QC .187"      | 0.7952"       | 287-D                       |
| 35-1303         | 35-1303-BU    | 4        | (On) Off         | SPST         | 10          | 6           |            | Black                | White O- (See Fig.)          | QC .187"      | 0.7952"       | 287-D                       |
| 35-1304         | 35-1304-BU    | 5        | On Off           | DPST         | 10          | 6           |            | Black                | White O- (See Fig.)          | QC .187"      | 0.7952"       | 287-E                       |
| 35-1305         | 35-1305-BU    | 6        | On Off On        | SPDT         | 10          | 6           |            | Black                | White -O=(See Fig.)          | QC .187"      | 0.7952"       | 287-F                       |
| 35-1307         | 35-1307-BU    | 3        | On Off           | SPST         | 10          | 6           |            | Amber (Lighted)*     | White O- (See Fig.)          | QC .187"      | 0.7952"       | 287-C                       |
| 35-1311         | 35-1311-BU    | 7        | On Off           | SPST         | 10          | 6           |            | Blk w/Red Indicator* | None                         | QC .187"      | 0.7952"       | 287-G                       |

Notes:  
(On)=Momentary On      \*=125V Lamp  
QC=Quick Connect

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

## AUTOMOTIVE/MARINE ROCKERS (Cont.)



## ROUND ROCKERS (Cont.)

