

Power It! Power Strip with 6 Outlets and 15-ft. Cord

MODEL NUMBER: **PS615**



Description

Tripp Lite's Power It! PS615 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 6 NEMA 5-15R outlets, 15-foot AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

Features

- 6 outlets
- 15-ft cord
- 15 amp resettable circuit breaker
- Green protection LED
- Can accommodate 1 large transformer plug without covering remaining outlets, 3 total transformers
- Keyhold support for wall mounting
- Lighted power switch
- 120V AC, 50/60Hz electrical compatibility
- UL certification

Specifications

General Info

Product Group

POWER STRIPS

Highlights

- 6 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 15 ft. power cord
- Keyhole mounting slots

Applications

- Offers a reliable, convenient and cost-effective method of power distribution for appliances, power tools, lighting and other electrical equipment in home, office or worksite.
- Unfiltered electrical pass-through makes the power strip ideal for distributing alternate waveform UPS or generator power to connected equipment.

Package Includes

- PS615 power strip
- Warranty information
- Instruction manual

OVERVIEW

Intended Application	Home/Office; Industrial/Factory Floor
----------------------	---------------------------------------

OUTPUT

Frequency Compatibility	50 / 60 Hz
Output (Watts)	1875
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Outlet Quantity / Type	6 NEMA 5-15R
Outlet Orientation	Single row of 6

INPUT

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.5
Input Cord Gauge Type	SJT 14AWG
Voltage Compatibility (VAC)	120

LEDS ALARMS & SWITCHES

Switches	Illuminated on/off switch controls power to all outlets
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff

PHYSICAL

Shipping Dimensions (hwd / in.)	13.2 x 5.8 x 1.8
Shipping Dimensions (hwd / cm)	33.52 x 14.73 x 4.57
Shipping Weight (lbs.)	1.77
Shipping Weight (kg)	.08
Unit Dimensions (hwd / in.)	10.8 x 1.85 x 1.23
Unit Dimensions (hwd / cm)	27.43 x 4.70 x 3.12
Unit Weight (lbs.)	1.6
Unit Weight (kg)	0.73
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting

Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Style	Strip
Outlets Measurement (Center to Center)	28.5mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between slots = 101mm, distance between slot height = 28mm
CERTIFICATIONS	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.