

AS6


8 mm

48 x 74 mm

15 mm

Polyamide 6.6

2 spring clamps
& 2 slots for interconnection

		UL ^①
22-8 AWG	0.5-6 sq.mm.	22-8 AWG
600V	800 V	600 V
50 A	41 A	50 A


AS2.5/3


5 mm

42 x 54 mm

12 mm

Polyamide 6.6

3 spring clamps
& 2 slots for interconnection

		UL ^① C US E220514
22-12 AWG	0.5-2.5 sq.mm.	22-12 AWG
600V	800 V	600 V
25A	24 A	25 A


AS2.5/4


5 mm

42 x 54 mm

12 mm

Polyamide 6.6

4 spring clamp connection



		UL ^① C US E220514
22-12 AWG	0.5-2.5 sq.mm.	22-12 AWG
600V	800 V	600 V
25 A	24 A	25 A



Cat. No.	Std. Pk.
AS6	50
EPAS6	50

Cat. No.	Std. Pk.
AS2.5/3	100
EPAS2.5	50

Cat. No.	Std. Pk.
AS2.5/4	100
EPAS2.5	50


CA702 50
CA802 50

CA702 50
CA802 50

CA702 50
CA802 50

CA801/3	100
CA801/3-3	100
CA901/3	100
CA901/4	100
CA901/5	100
MT8	100
MT6F	10

CA801/1	100
CA801/1-3	100
CA901/1	100
CA901/5	100
CA901/6	100
MT5	100
MT6F	10

^① UL recognition in progress.