Tyco Electronics

408–8787
17 JUN 09   Rev A
CU

TO BE SOLD ONLY WITH INSTALLATION INSTRUCTIONS

UL 424C LISTED

**Pressure Type Wire Connectors
PLASTI–GRIP* Vinyl Terminals and
Butt and Parallel Splices**
(Use Tooling for PLASTI–GRIP* Connectors,
PIDG* Tool, or TETRA–CRIMP*‡ Tool)

**UL Listed Wire Combinations
Wire Sizes 22–12 AWG**

WIRE		CONNECTOR RATING
SIZE RANGE (AWG)	TYPE	
22–10‡‡	SOLID OR STRANDED	90°C [194°F] Max (Vinyl)
12	SOLID	600 Volts Max Building Wiring 1000 V Fixture or Sign

NOTE: Terminals used with wire sizes 22–16 AWG are stamped with 22–18 in accordance with SAE–AS7928 (formerly MIL–T–7928).

‡ This tool crimps a terminal with stranded wire only.

‡‡ Only use stranded wire size 12 AWG with spring spade terminals.