

~~THIS DRAWING IS UNPUBLISHED.~~

RELEASED FOR PUBLICATION

AUG. 25, 1981.



© COPYRIGHT 1971

BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓		D	REDRAWN & REV.	8-24-81	<i>SWB</i>
✓	✓		E	REVISED FERRULE	10-7-81	<i>WTW</i>

FOR USE WITH:
RG-223/U, 142A/U & 142B/U

ASSEMBLED VIEWSTRIP LENGTH

* SUPPLIED BY DANIELS MFG. CORP.
2266 FRANKLIN ROAD
BLOOMFIELD HILLS, MICH. 48013

1	225592-2	SEAL	4
1	1-225560-3	FERRULE	3
1	225800-2	CONTACT	2
1	225797-1	SHELL ASS'Y	1
QTY.	PART NO OR IDENTIFYING NO	NOMENCLATURE OR DESCRIPTION	ITEM NO

CENTER CONTACT CRIMPING TOOL:	M 2252012-C1 SETTING NO 5 POSITIONER 4344 * (AMP EQUIV. 1-61966-6) SEE I.S. 2348	220066-2
FERRULE CRIMPING TOOL:	220066-1 or 220066-2 CRIMP B	
	RG-223/U	RG-142A/U & 142B/U

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.
TOLERANCES ON:
DECIMALS ±
ANGLES ±

CONTRACT NO

DR

CHK

APPD

APPD

DSGN APPD

OTHER APPD

AMP

AMP INCORPORATED
Harrisburg, Pa. 17105

NAME

ARINC COAXIAL
SOCKET
SIZE 7

SIZE

B

FSCM NO

00779

DRAWING NO

225796-2

SCALE NTS

WT. .14 OZ

SHEET