

**ebm-papst St. Georgen GmbH & Co. KG**

Hermann-Papst-Str. 1

D-78112 St. Georgen

Phone +49 (0) 7724 81-0

Fax +49 (0) 7724 81-1309

info2@de.ebmpapst.com

www.ebmpapst.com

Nominal data

Type	8880 TA	
Phase		1~
Nominal voltage	VAC	230
Frequency	Hz	50
Speed (rpm)	min ⁻¹	1650
Power consumption	W	9.0
Min. ambient temperature	°C	-10
Max. ambient temperature	°C	80
Air flow	m ³ /h	23
Sound pressure level	dB(A)	15

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · ce = Customer equipment
Subject to change



Technical description

Weight	0.370 kg
Dimensions	Ø 76 x 37 mm
Impeller material	Metal
Airflow direction	Intake over mounting bracket.
Direction of rotation	Clockwise, viewed toward rotor
Storage	Sintec sleeve bearing system
Service life L10 at 40 °C	60000 h
Service life L10 at maximum temperature	25000 h
Cable	2 leads AWG 28, TR 64
Motor protection	Protected from overload by impedance protection
Approval	VDE, CSA, UL, CE

Product drawing

