


60x60x20mm Series

Spot cooling, also suitable for small space requirements, desktop and PC.

EXTERNAL DIMENSIONS



Housing	Impeller	Bearing Available	Lead Wire	Protection	Operating Temp*	Voltage Available
Plastic (UL: 94V-0)	Plastic (UL: 94V-0)	Ball/Hypro/Sleeve	UL1007 AWG24	Current Limit	-10°C~70°C	5V, 12V, 24V

*: -10°C~60°C for fans with sleeve/ball combination bearings.

SPECIFICATIONS (NOMINAL)

Frame Size	Model No.	Bearing type	Voltage (V)	Current (A)	Power (W)	Speed (rpm)	Air flow (CFM)	Pressure (mmAq)	Noise (dB/A)	Weight (g)
60x60x20mm	AD0605HX-C70GL	Hypro	5	0.30	1.50	4500	16.4	3.53	29.7	50
60x60x20mm	AD0605MX-C70GL	Hypro	5	0.24	1.20	3900	14.5	2.82	25.7	50
60x60x20mm	AD0612HX-C70GL	Hypro	12	0.16	1.92	4500	16.4	3.53	29.7	50
60x60x20mm	AD0612MX-C70GL	Hypro	12	0.13	1.56	3900	14.5	2.82	25.7	50
60x60x20mm	AD0612LX-C70GL	Hypro	12	0.08	0.96	3500	13.3	2.44	21.6	50
60x60x20mm	AD0624HX-C70GL	Hypro	24	0.09	2.16	4500	16.4	3.53	29.7	50

Specifications subject to change without notice.

* Noise is measured at the distance of one (1) meter from the axis of intake.

PERFORMANCE CURVES

* MOTOR PROTECTIVE CIRCUIT AND THIRD LEAD WIRE

0	1	2	3	4	6	7	8	9	A
✓	✓	✓	✓	✓	✓	✓		✓	

* SAFETY APPROVALS

✓	✓	✓	✓

