


Part No.	(5)Length	Part No.	(5)Length
3180-0.5	0.5M	3180-15	15M
3180-1	1M	3180-20	20M
3180-2	2M	3180-25	25M
3180-3	3M	3180-30	30M
3180-5	5M	3180-50	50M
3180-10	10M		



Specification :

- Connector Type : LC/PC Multimode.
- Cable Marker.
- Cable Type :
 - Zipcord cable, $\phi 3.0\text{mm}$, 62.5/125um Multimode.
 - Cable Jacket : Gray color, LSZH material.
- Shrink Tube.
- Length : xM.

Performance :

- Insertion Loss : $< 0.5 \text{ dB}$.
- Fiber Extention : $-0.05\text{um} < H < +0.05\text{um}$.
- Ferrule End-face Radius : $7 < R < 25\text{mm}$.
- Apex Offset : $< 50\text{um}$.
- Increase in insertion loss after 500 mating : 0.2 dB Max.
- Operation Temperature : -20°C to $+70^\circ\text{C}$.
- Storage Temperature : -40°C to $+80^\circ\text{C}$.

RoHS Compliant

	DSGN	CSQ	21.MAY.2007	ITEM NO: 3180	
	CHK	Maer	21.MAY.2007		
	UNIT	M/M	APPR	Yty	LC to LC Duplex patch cord
	SCALE	1/1	DWG NO: 3180		
Videk Ltd					