




MATERIAL:

Thermoplastic 25%rebroye maxi

TEMPERATURE RANGE:


-Climatic category -55°/ +125°

PACKAGING:

Per 1 piece

COLOUR

Black



Dimensions are in millimeters

Shell size	Number of contacts	A ^{+0.9 -0.2}	B ^{+0.10 0}	C ^{±0.05}	D ^{±0.10}	E ^{±0.10}	F ^{±0.10}	G ^{±0.10}	PART NUMBER
E	09	30.60	12.50	24.99	19.00	10.50	9.90	18.20	8630-211B
A	15	38.90	12.50	33.32	20.60	12.50	9.90	22.80	8630-212B
B	25	52.80	12.50	47.04	23.60	17.00	9.90	29.40	8630-213B
C	37	69.10	12.50	63.50	29.00	24.00	9.90	37.00	8630-214B
D	50	66.70	15.30	61.11	28.00	24.00	12.70	35.00	8630-215B

European Views

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	PESSON	2003/12/30	ANGULAR	0.X	±0.1	size
Eng	PESSON	2003/12/30	LINEAR	0.XX	±0.1	A3
Chr	LEGARE	2003/12/30	0.XX ±2°	0.XXX	±0.1	ECN
Appr	LEGARE	2003/12/30	Product family	SUB	Spec ref	-
			MONOBLOC PLASTIC HOODS			Rev.
			FOR POTTING RIGHT ANGLE EXIT			C
			catalog no	-	CUSTOMER	sheet 1 of 1

rev	ecn no	dr	date
B	-	MPE	2003/12/30
C	LS07-0094	MPE	2007/04/20
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

REV F - 2006-04-17