

## Housing - HC-B 24-TMQ-76/O1STM25S - 1647200

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON sleeve housing B24, with double locking latch, height 76 mm, with thread 1x M25, lateral conductor exit

The illustration shows a product version with straight conductor exit



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 PCE                                                                                                   |
| GTIN                                 | <br>4 017918 957247 |
| Weight per Piece (excluding packing) | 409.4 GRM                                                                                               |
| Custom tariff number                 | 85389099                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### Dimensions

|        |        |
|--------|--------|
| Height | 76 mm  |
| Width  | 43 mm  |
| Length | 120 mm |

#### Ambient conditions

|                                      |                   |
|--------------------------------------|-------------------|
| Degree of protection of housing (IP) | IP65              |
| Ambient temperature (operation)      | -40 °C ... 125 °C |

#### General

|              |                                                 |
|--------------|-------------------------------------------------|
| Note         | For contact inserts HC-B24, BB46, D64, DD108, M |
| Design       | B24                                             |
| Housing type | Sleeve housings                                 |
| Locking type | With double locking latch                       |

## Housing - HC-B 24-TMQ-76/O1STM25S - 1647200

### Technical data

#### General

|                              |                             |
|------------------------------|-----------------------------|
| No. of cable exits           | 1                           |
| Cable exit                   | Lateral                     |
| Screw connection             | None                        |
| Type of the screw connection | 1x M25                      |
| Housing material             | Aluminum die-cast           |
| Housing surface material     | Powder-coated, gray         |
| Material lock                | Stainless steel, handle: PA |
| Material grip body interlock | PA-GF                       |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440209 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11     | 31261502 |
| UNSPSC 12.01  | 31261502 |
| UNSPSC 13.2   | 31261502 |

### Accessories

#### Accessories

Full screw connection

## Housing - HC-B 24-TMQ-76/O1STM25S - 1647200

### Accessories

Cable gland - HC-K-KV-M25(11-17) - 1690639



Plastic screw connection up to 5 bar, thread length: 8 mm, cable diameter: 11 - 17 mm, WAF 29, screw connection: M25

---

Cable gland - HC-M-KV-M25(11-16) - 1690574



Metal screw connection up to 5 bar, thread length: 7 mm, cable diameter: 11 - 16 mm, WAF 27, screw connection: M25

---

Cable gland - HC-M-KV-M25(14-21) - 1646007



Metal screw connection up to 5 bar, thread length: 7 mm, cable diameter: 14 - 21 mm, WAF 34, screw connection: M25

---

Cable gland - HC-M-KV-M25(1ASI) - 1584020



Metal screw connection for an AS-Interface flat-ribbon conductor, thread type M25

---

### Multiple screw connection

Cable gland - HC-M-KV-M25(1X10/1X11) - 1580228



Special cable screw connection M25, brass nickel-plated, grommet with 10 mm and 11 mm holes

---

## Housing - HC-B 24-TMQ-76/O1STM25S - 1647200

### Drawings

Dimensioned drawing

