





International size reference: 1/6D, ER32L100

(Typical values @+25°C for batteries stored for one year or less)

■	Nominal capacity @ 1 mA, to 2 V	1.5 Ah
■	Rated voltage	3.6 V
■	Maximum recommended continuous current	10 mA
■	Maximum pulse current capability	50 mA
■	Weight	21 g (0.74 oz)
■	Volume	8.2 cc
■	Operating temperature range	-55 °C to +125 °C
■	Li metal content	approx. 0.5 g
■	U.L. Component Recognition, MH 12193	



Extended Operating Range

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

ECN 1501187 Rev. A 01/06