


Series 1000 Neon Lamps



UL File No. E20325, CSA File No. 13346. White nylon housing will snap-fit into a .500/.505" diameter hole in panels .020/.100" thick. **Bezel:** Stainless Steel.

Pilot Lamps with Low-Profile Lenses

Stock No.	Mfr.'s Type	Lens Color	VAC	EACH		
				1-99	100-499	500-999
679-5050	1030D1†	Red	105-125	1.90	1.71	1.56
679-5060	1030D3†	Amber	105-125	1.90	1.71	1.56
679-5070	1030D4†	White	105-125	1.90	1.71	1.56
679-5080	1032D5†*	Green	105-125	2.92	2.57	2.34
679-5095	10300D1†	Red	105-125	2.06	1.86	1.69
679-5065	10300D3†	Amber	105-125	2.06	1.86	1.69
679-5075	10300D4†	White	105-125	2.06	1.86	1.69
679-5085	10320D5†*	Green	105-125	1.93	1.73	1.58
679-9768	1031D1†	Red	208-250	1.90	1.71	1.56
679-9769	1031D3†	Amber	208-250	1.90	1.71	1.56
679-9772	10310D1†	Red	208-250	2.06	1.86	1.69
679-9774	10330D5†*	Green	208-250	3.04	2.73	2.49

Pilot Lamps with High-Hat Lenses

Stock No.	Mfr.'s Type	Lens Color	VAC	EACH		
				1-99	100-499	500-999
679-5100	1050C1†	Red	105-125	1.90	1.71	1.56
679-5130	1050C2†	Clear	105-125	1.90	1.71	1.56
679-5110	1050C3†	Amber	105-125	1.90	1.71	1.56
679-5120	1050C4†	White	105-125	1.79	1.61	1.47
679-5140	1052C5†*	Green	105-125	3.04	2.78	2.49
679-5105	1050QC1†	Red	105-125	1.56	1.41	1.28
679-5135	1050QC2†	Clear	105-125	1.95	1.75	1.59
679-5115	1050QC3†	Amber	105-125	2.06	1.86	1.69
679-5125	1050QC4†	White	105-125	2.06	1.86	1.69
679-5145	1052QC5†*	Green	105-125	3.04	2.73	2.49
679-9781	1051C1†	Red	208-250	1.90	1.71	1.56
679-9782	1051C3†	Amber	208-250	1.90	1.71	1.56
679-9783	1053C5†*	Green	208-250	2.86	2.57	2.34
679-9784	1051QC1†	Red	208-250	2.18	1.96	1.78
679-9785	1051QC3†	Amber	208-250	2.06	1.86	1.69
679-9786	1053QC5†*	Green	208-250	3.04	2.73	2.49

Pilot Lights with Dome Lenses


679-5150	1050A1†	Red	105-125	1.90	1.71	1.56
679-5160	1050A3†	Amber	105-125	1.90	1.71	1.56
679-5170	1050A4†	White	105-125	1.90	1.71	1.56
679-5190	1052A5†*	Green	105-125	2.86	2.57	2.34
679-5155	1050QA1†	Red	105-125	2.06	1.86	1.69
679-5185	1050QA2†	Clear	105-125	2.06	1.86	1.69
679-5165	1050QA3†	Amber	105-125	2.06	1.86	1.69
679-5195	1052QA5†*	Green	105-125	2.86	2.57	2.34
679-9787	1051A1†	Red	208-250	2.02	1.82	1.65
679-9788	1051A3†	Amber	208-250	1.43	1.29	1.17
679-9789	1053A5†*	Green	208-250	3.04	2.73	2.49
679-9790	1051QA1†	Red	208-250	2.06	1.86	1.69
679-9791	1051QA3†	Amber	208-250	2.06	1.86	1.69
679-9792	1053QA5†*	Green	208-250	2.86	2.57	2.34

Pilot Lights with Square Lenses

679-6060	1050N1†	Red	105-125	2.06	1.86	1.69
679-6070	1050N3†	Amber	105-125	2.06	1.86	1.69
679-6090	1052N5†*	Green	105-125	3.04	2.73	2.49
679-6065	1050ON1†	Red	105-125	2.24	2.02	1.84
679-6075	1050ON3†	Amber	105-125	2.24	2.02	1.84
679-6095	1052ON5†*	Green	105-125	3.22	2.90	2.63

*Incorporates G2B lamp and resistor. †With wire leads 4.4/4.8" long, striped 43/57". ‡With .187"-.020" tinned brass terminals.

Glo-Dot Miniature Neon Pilot Lights Series 2150, 2110



These miniature neon pilot lights are engineered for long service reliability. Rugged, unaffected by shock and vibration. Two lens shapes, flush and high-hat which are available in five colors — red, amber, white, clear and green. Mounting hole is .31" minimum diameter. **Average Operating Life:** 25,000 hours.

UL recognized and CSA approved. Supplied with push-on speed nut (SN1287). Units supplied with 4.4"-4.8" wire terminals, stripped 1/2" or .187"-.020" tinned brass terminals.

Stock No.	Mfr.'s Type	Lens Color	VAC	EACH		
				1-99	100-499	500-999
679-6400	2150A1	Red	105-125	2.02	1.82	1.65
679-6405	2150A3	Amber	105-125	2.02	1.82	1.65
679-6410	2150A4	White	105-125	1.90	1.71	1.56
679-6415	2150A2	Clear	105-125	2.02	1.82	1.65
679-6420	2152A5*	Green	105-125	3.24	2.97	2.65
679-6611	2110A1	Red	105-125	1.43	1.29	1.17
679-6613	2110A3	Amber	105-125	1.79	1.61	1.47
679-6615	2110A4	White	105-125	1.88	1.69	1.54
679-6617	2110A2	Clear	105-125	1.88	1.69	1.54
679-6620	2112A5*	Green	105-125	2.86	2.57	2.34
679-6500	2150QA1	Red	105-125	2.18	1.99	1.78
679-6505	2150QA3	Amber	105-125	2.18	1.99	1.78
679-6510	2150QA4	White	105-125	2.06	1.86	1.69
679-6520	2152QA5*	Green	105-125	3.40	3.06	2.78
679-6700	2110QA1	Red	105-125	2.06	1.86	1.69
679-6705	2110QA3	Amber	105-125	2.06	1.86	1.69
679-6710	2110QA4	White	105-125	1.93	1.73	1.58
679-6715	2110QA2	Clear	105-125	2.06	1.86	1.69
679-6720	2112QA5*	Green	105-125	3.01	2.71	2.47
679-9700	2151A1	Red	208-250	2.02	1.82	1.65

*Incorporates G2B lamp and resistor. †Incorporates T2B lamp and resistor.

Stock No.	Mfr.'s Type	Lens Color	VAC	EACH		
				1-99	100-499	500-999
679-9701	2151A2	Clear	208-250	2.02	1.82	1.65
679-9702	2151A3	Amber	208-250	2.02	1.82	1.65
679-9703	2151A4	White	208-250	1.90	1.71	1.56
679-9704	2153A5*	Green	208-250	3.24	2.92	2.65
679-9705	2153A6†	Blue	208-250	3.24	2.92	2.65
679-9706	2111A1	Red	208-250	1.43	1.29	1.17
679-9707	2111A2	Clear	208-250	1.79	1.61	1.47
679-9708	2111A3	Amber	208-250	1.88	1.69	1.54
679-9709	2111A4	White	208-250	1.88	1.69	1.54
679-9710	2113A5*	Green	208-250	2.86	2.57	2.34
679-9711	2113A6†	Blue	208-250	2.86	2.57	2.34
679-9712	2151QA1	Red	208-250	2.18	1.96	1.78
679-9713	2151QA3*	Amber	208-250	2.06	1.86	1.69
679-9714	2151QA4	White	208-250	2.18	1.96	1.78
679-9715	2153QA5*	Green	208-250	3.40	3.06	2.78
679-9716	2111QA1*	Red	208-250	1.93	1.73	1.58
679-9718	2111QA3	Amber	208-250	1.93	1.73	1.58
679-9719	2111QA4	White	208-250	2.06	1.86	1.69
679-9720	2113QA5*	Green	208-250	3.20	2.88	2.61
—	—	—	—	—	—	—