


**Panel Mount Indicator, Non-Relampable
Neon Technology
Mounting Hole, Ø 0.500"**



All dimensions are in inches



RoHS
COMPLIANT

Recommended panel thickness: 0.030" to 0.090"

.187 terminals are standard

Storage temperature T_{STG} : -25°C - +80°C

Ambient temperature T_A : -20°C - +60°C

Voltage tolerance V_{OP} : $\pm 10\%$

[illegible]

Body Material: Nylon, white
 Lens Material: Polycarbonate
 Bezel Material: Stainless steel
 Note: .250 quick connects available upon request

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.

Options: Additional options and lens styles available.
Please contact Wamco for more information.

Drawn	SC	03/01/10	Panel Mount Indicators Neon	Datasheet: WL-105XQAX Series	Rev: 1
Checked	EB	03/01/10			
Approved	EB	03/02/10			