



**Euro-connector-block 6 mm², divisible
1 - 12-poles, pole-distance 11,5 mm,
solid fixing-strip,
also with wire-protection (DSS)**

Casing : natural polyamide

Connecting body : steel zinc-plated


Screw : M 3,5 nickel-plated steel

Wire-protection : chrome-nickel-steel

This connector is available from 1 - 12-poles or can be cut according to your requirements. Delivery will be effected ready for installation with slightly twisted screws, which are protected against self-loosening in the insulation-part.

Wire-protection (DSS) is necessary for fixing of flexible wires.





Accessories as description-labels, cover-caps and components are available.



41A
750V

PTI 250

T110



No. of poles	Length	Article-no.	kg/100 pcs.	Article-no. with DS	kg/100 pcs.	Article-no. with DSS	kg/100 pcs.	Article-no. with MB	kg/100 pcs.	Pkg. qty.
1	8,0	1013100001	0,43	-	-	1013103001	0,44	1013106001	0,43	1000
2	19,5	1013100002	0,88	-	-	1013103002	0,90	1013106002	0,88	1000
3	31,0	1013100003	1,32	-	-	1013103003	1,35	1013106003	1,32	500
4	42,5	1013100004	1,76	-	-	1013103004	1,80	1013106004	1,76	200
5	54,0	1013100005	2,20	-	-	1013103005	2,25	1013106005	2,20	200
6	65,5	1013100006	2,64	-	-	1013103006	2,70	1013106006	2,64	200
7	77,0	1013100007	3,08	-	-	1013103007	3,15	1013106007	3,08	100
8	88,5	1013100008	3,52	-	-	1013103008	3,60	1013106008	3,52	100
9	100,0	1013100009	3,96	-	-	1013103009	4,05	1013106009	3,96	100
10	111,5	1013100010	4,40	-	-	1013100010	4,50	1013100010	4,40	100
11	123,0	1013100011	4,84	-	-	1013103011	4,95	1013106011	4,84	100
12	134,5	1013100012	5,28	-	-	1013103012	5,40	1013106012	5,28	100

