

GP Batteries

Data Sheet


Model No.: GP14G

NO MERCURY ADDED

Description	: Mercury Free Extra Heavy Duty Battery, C Size
Chemical System	: Zinc Chloride
Nominal Voltage	: 1.5 Volts
Nominal Dimensions	: Ø26.2 mm x 50.0 mm
Terminals	: Protruded positive(+) and flat negative(-) contacts
Jacket	: Metal jacket with PVC tube insulation
Applications	: All electronic devices, e.g. transistor radios, cassette recorders, toys, alarm clocks, lighting & torches, portables fans.
Shelf Life	: 24 months
Average Weight	: 49g
Date Code	: Unless otherwise specified, every battery will carry an expiry date code for 24 months. (e.g. a battery manufactured on January 1999 will carry an expiry code of 01-01.) 01 stands for January, 01 stands for 2001

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
3.9 Ohms	24 Hrs/ Day	0.9V	320 Mins



At 20°C within 30 days of manufacture

Cross References:

GP	JIS	IEC	Eveready
14G	R14P	R14	1235

