

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200860111](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 24 AWG, PVC Cable, 10.0m (32.81') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [120086](#)
Connector End A Nano-Change (M8)
Connector End B Pigtail
IP Rating IP68
Material - Contact Copper Alloy
Overview [Brad Nano-Change \(M8\) Products](#)
Product Name Nano-Change (M8)
Region America
Type Single Ended
UPC 78678811280

Physical

Cable Diameter 4.32mm (.170")
Cable Length 10.0m (32.81')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Pigtail
Keyway A-coded
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body TPE
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Orientation Straight to Pigtail
Poles 3
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 24
Wire/Cable Type UL 2661

Electrical


Current - Maximum per Contact 3.0A
Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 403000A10M100

Reference - Drawing Numbers

Sales Drawing 1200860594-000, SD-120086-102



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120086](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION