




AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL

PRODUCT INFORMATION OR

COPIES OF DRAWINGS

AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER

1-800-522-6752

FOR APPLICATION

TOOLING INFORMATION

TOOLING ASSISTANCE CENTER

1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING

TEMPERATURE:

105° C MAX

VOLTAGE RATING:

300 V MAX

WIRE CROSS SECTIONAL AREA RANGE:

0.26-1.65mm<sup>2</sup> [509-3,260] CIR MILS

SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

INCHES

TOLERANCES UNLESS

OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .008

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

BODY & SLEEVE:

COPPER PER ASTM B152

INSULATION: NYLON-RED

BODY: TIN PLATE PER

ASTM B545

DWN

JR RUTH

24JUL02

CHK

T MICHIELUTTI

24JUL02

APVD

T MICHIELUTTI

24JUL02

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

SCALE

8:1

SHEET

1 OF 1

REV

S1

TE

TE Connectivity

WIRE TERMINAL, PIDG,

FLANGED SPADE, 22-16 AWG

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-32562

RESTRICTED TO

-