


## Countersunk head self tapping screws - PoziDriv® - Pointed



DIN 7982 C Z  
ISO 7050 C Z  
BS 4174 AB

## Materials and Finishes

Case hardened steel/Zinc & clear de-embrittled  
Stainless steel/Self colour

## Dimensions

|            |      |      |      |     |      |       |       |       |
|------------|------|------|------|-----|------|-------|-------|-------|
| d          | 2.2  | 2.9  | 3.5  | 3.9 | 4.2  | 4.8   | 5.5   | 6.3   |
| d          | No.2 | No.4 | No.6 | -   | No.8 | No.10 | No.12 | No.14 |
| D max      | 4.3  | 5.5  | 6.8  | 7.5 | 8.1  | 9.5   | 10.8  | 12.4  |
| H max      | 1.3  | 1.7  | 2.1  | 2.3 | 2.5  | 3     | 3.4   | 3.8   |
| Recess No. | 1    | 1    | 2    | 2   | 2    | 2     | 3     | 3     |

## Preferred Lengths

|               |      | Thread (d) |       |       |     |       |       |     |     |
|---------------|------|------------|-------|-------|-----|-------|-------|-----|-----|
|               |      | 2.2        | 2.9   | 3.5   | 3.9 | 4.2   | 4.8   | 5.5 | 6.3 |
| Length<br>(L) | 4.5  | ST         | ST    |       |     |       |       |     |     |
|               | 6.4  | ST         | ST A2 | ST    |     |       |       |     |     |
|               | 7.9  | ST         | ST A2 | ST    |     |       |       |     |     |
|               | 9.5  | ST         | ST A2 | ST A2 | ST  | ST A2 |       |     |     |
|               | 12.7 | ST         | ST A2 | ST A2 | ST  | ST A2 | ST A2 | ST  |     |
|               | 15.9 | ST         | ST A2 | ST A2 | ST  | ST A2 | ST A2 | ST  |     |
|               | 19   |            | ST A2 | ST A2 | ST  | ST A2 | ST A2 | ST  | ST  |
|               | 22.2 |            | ST    | ST    | ST  | ST    | ST    |     |     |
|               | 25.4 |            | ST A2 | ST A2 | ST  | ST A2 | ST A2 | ST  | ST  |
|               | 31.8 |            |       | ST    | ST  | ST A2 | ST A2 | ST  | ST  |
|               | 38   |            |       | ST    | ST  | ST A2 | ST A2 | ST  | ST  |
|               | 44.5 |            |       |       |     | ST A2 | ST A2 | ST  | ST  |
|               | 50.8 |            |       |       |     | ST A2 | ST A2 | ST  | ST  |
|               | 57   |            |       |       |     |       | ST    | ST  |     |
|               | 63   |            |       |       |     |       | ST    | ST  | ST  |

|  |    |  |  |  |  |  |    |    |    |
|--|----|--|--|--|--|--|----|----|----|
|  | 70 |  |  |  |  |  |    |    |    |
|  | 75 |  |  |  |  |  | ST | ST | ST |

ST - Steel, Zinc & clear de-embrittled  
A2 - Stainless steel