



Standard Extra Low Voltage A60

Standard ELV 60W E27/BRC 50V A60 CL 1CT

Clear lamp (A-bulb) for operation on voltages of 24 and 50V

Product data

• General Characteristics

Cap-Base	ES [ES]
Cap-Base Information	Brass [Brass Cap]
Bulb	A60 [A 60mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Average Lifetime	1000 hr

• Light Technical Characteristics

Lamp Luminous Flux	810 Lm
--------------------	--------

• Electrical Characteristics

Lamp Wattage	60 W
Voltage	50 V
Dimmable	yes

• Product Dimensions


Overall Length C	107.5 (max) mm
Diameter D	60 mm

• Product Data

Order code	101884 84
Full product code	871150010188484
Full product name	Standard ELV 60W E27/BRC 50V A60 CL 1CT
Order product name	Stan ELV 60W E27/BRC 50V A60 CL 1CT
Pieces per pack	1
Packing configuration	12X10F
Packs per outerbox	120
Bar code on pack - EAN1	8711500101884
Bar code on intermediate packing - EAN2	8711500154996
Bar code on outerbox - EAN3	8711500348999
Logistic code(s) - 12NC	920021025303
ILCOS code	IAA/C-60-50-E27-60
Net weight per piece	28.000 gr

Dimensional drawing

Dimensional drawing



E27, A60

Product	C (Max)	D (Norm)
ELV 60W E27/BRC 50V A60 CL	107.5	60



E27



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, July 31
data subject to change