

Receptacles

Features:

- DIN Rail, Panel Mount or Wall Mount
- Rating: 15A/125V AC
- Finger Protection: IP54
- Available in 3 colors.

PANEL MOUNT



WALL MOUNT



DIN RAIL MOUNT



External Dimension (HxWxL mm)

36.5 x 61.5 x 50

Stripping Length

10 mm

Insulation Material

Thermoplastic

Type of Connection

3 screw clamps

Approvals*

c  US
E154664

Voltage Rating

125 V

Current Rating

15 A

50 x 71 x 53.5

10 mm

Thermoplastic

3 screw clamps

c  US
E154664

125 V

15 A

58.5 x 84 x 53.5

10 mm

Thermoplastic

3 screw clamps

c  US
E154664

125 V

15 A

Cat. No.

Std. Pk.

Cat. No.

Std. Pk.

Cat. No.

Std. Pk.

Complete Kit:

Blue
Gray
Black

PMRBU 1
PMRGR 1
PMRBA 1

WMRBU 1
WMRGR 1
WMRBA 1




DMRBU 1
DMRGR 1
DMRBA 1

Optional Accessory
Sealing Gasket
for Panel Mount Receptacles

SEALGASK 1


Includes Sealing Gasket

Includes Sealing Gasket



*UL approval applies to outlet only, not enclosure or DIN rail clip.


PANEL MOUNT




**Wiring of
Receptacles**



WALL MOUNT



DIN RAIL MOUNT



¹ Optional Sealing Gasket for wet environments.