



THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Updated Specifications	08-31-11	LY



NOTES:

MATERIAL:

MOULDING: NYLON, FLAMMABILITY RATING UL94V-0
CONTACTS: BRASS, CLEAN
RATING: 10A 250V AC
INSULATION RESISTANCE: >1000 M OHM
CONTACT RESISTANCE: < 10m OHM
A.C. BREAKDOWN:
POLE-POLE: 4.5kV
POLES-ACCESSIBLE: 4kV
OPERATING TEMPERATURE: -40° C TO +70° C
WITHDRAWL FORCE: 10N (MIN), 50N (MAX)
APPROVALS: UL, CSA, VDE
FOR USE WITH 18 AWG CORDAGE ONLY
RoHS COMPLIANT

CONTROLLED

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION		
		Part Number:	705-00/00	RoHS Compliant
0-1	0.15	Description: REWIRABLE PLUG ASSEMBLY		
1-6	0.20			
6-18	0.30	Drawn / Date B.Zhang 12-30-02	UNIT: mm	REV.C
18-50	0.50		Checked / Date	Approved / Date
50-120	0.70			
120-250	0.90			
250-500	1.20			