


General ordering data

Order No.	8574070000
Part designation	MCZ R 48...110Vdc 1NO TRAK
Version	Relays, 1 NO contact, 48...110 V DC , 6 A, Tension clamp connection
EAN	4032248232932
Qty.	10 pc(s).

Input

Rated control voltage	48...110 V DC
Pull-in (sparkover) / drop-out voltage DC coil	> 25 V / < 6 V
Rated current DC	< 3 mA
Power rating	< 300 mW
Status indicator	Green LED
Max. reset time after voltage interruption	10 ms

Output

Bounce times	typically 1 ms
Continuous current	6 A
Max. switching frequency at rated load	0.1 Hz
Min. switching power	12 V / 100 mA
Switch-off delay	typ. 75 ms
Switch-on delay	< 4 ms

Contact data

Number of contacts	1
Contact base material	AgSnO
Mechanical service life	20*10 ⁶ switching cycles

Rated data

Climate	95% for 30 days, minimal condensation to EN 50155
Conductor	AWG 26...16
Connection system	Tension clamp connection
Flexible, max.	1.5 mm ²

Rated data

Solid, max.	1.5 mm ²
Storage temperature	-40 °C...+85 °C

Insulation coordination (EN 50 178)

Dielectric strength to mounting rail	4 kV / 1 min.
Impulse withstand voltage	4 kV (1.2/50 µs)
Overvoltage category	III
Pollution severity	2
Protection class	IP 20
Rated voltage	300 V
Secure separation acc. to VDE 0106 part 101	Yes

Dimensions

Clamping range, max.	2.5 mm ²
Clamping range, min.	0.5 mm ²
Clamping range, nom.	1.5 mm ²
Length	91 mm
Height	63.2 mm
Width	6 mm

Approvals

Approvals institutes	n.a.
----------------------	-------------

Classifications

ETIM 2.0	EC001437
ETIM 3.0	EC001437
eClass 4.1	40-02-06-14
eClass 5.0	27-37-16-01
eClass 5.1	27-37-16-01

Similar products

Order No.	Part designation	Version
8713890000	MCZ R 24Vdc 1CO TRAK	Relays, 1 CO contact, 24 V DC , 6 A, Tension clamp connection
8499550000	MCZ R 24Vdc 1NO TRAK	Relays, 1 NO contact, 24 V DC , 6 A, Tension clamp connection
8713900000	MCZ R 36Vdc 1CO TRAK	Relays, 1 CO contact, 36 V DC , 6 A, Tension clamp connection
8582130000	MCZ R 36Vdc 1NO TRAK	Relays, 1 NO contact, 36 V DC , 6 A, Tension clamp connection
8713910000	MCZ R 48...110Vdc 1CO TRAK	Relays, 1 CO contact, 48...110 V DC , 6 A, Tension clamp connection