




ETA-USA

HIGH QUALITY SWITCHING POWER SUPPLIES

Environmental Specification								
Operating Temperature		0 to +55°C ambient						
Storage Temperature		-10 to +75°C ambient						
Derating		43°C ~ 55°C : 2.5%/°C.						
Operating Humidity		20% ~ 95%						
Storage Humidity		10% ~ 95% (non condensing)						
Cooling		Natural Cooling						
Protection/Control Specification								
Over Voltage Protection		+5.8~7.0	+8.6~10.5	+10.4~12.6	+13.8~17.5	+17.3~21.0	+20.7~25.2	+27.6~33.6
Short Circuit Protection		Hiccup, recovers automatically after fault condition has been removed.						
Safety		UL 1950 3rd, CSA C22.2 No.950-95 3 rd, TUV EN 60950, IEC 60950, EMKO-TSE (74-SEC)207/94 approved.						
M.T.B.F.		550K hours						
EMC	EMI	EN 55022 : EN 61000-3-2,3、FCC CFR 47 PART15 CLASS B、CNS13438 CALSS B.						
	EMS	EN 55024 : EN-61000-4-2,3,4,5,6,8,11						
Dimension		86 x 50 x 33 mm[3.39 x 1.97 x 1.30 inch]						

DIMENSION DIAGRAM



NOTE :

1. ENCLOSURE COLOR : BLACK.
2. AC INLET : IEC 320 C14 STANDARD.
3. DC PLUG. (I.D.=2.5mm ; O.D.=5.5mm)
4. UNIT : mm.



ETA USA

16170 Vineyard Blvd. Suite 180, Morgan Hill, CA 95037

Phone: 1-800-ETA-POWER, (408) 778-2793 Fax: (408) 779-2753

Visit us at: www.eta-usa.com

email at: sales@eta-usa.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETA-USA:](#)

[DTM15-7.5SX-SP](#) [DTM15-5SX-SP](#)