




## K44 Series Right Angle PCB Mount .590" Footprint

### Ordering Information

| K44    | — | B          | 25                 | S            | — | P                |
|--------|---|------------|--------------------|--------------|---|------------------|
| Series |   | Shell Size | Number of Contacts | Contact Type |   | Mounting Options |

#### Series

K44 - Kycon D-Subminiature Connector, Right Angle, PCB Termination, .590 Footprint

#### Shell Size

- E - 9 Contacts
- A - 15 Contacts
- B - 25 Contacts
- C - 37 Contacts

#### Number of Contacts

9, 15, 25, 37

#### Contact Type

- P - Pin Contact (Plug)
- S - Socket Contact (Receptacle)

#### Mounting Options (see page 36)

#### Plating Options

| Designator | Plating Description                                                                                |
|------------|----------------------------------------------------------------------------------------------------|
| Standard   | Gold flash over nickel on contacts. Gold flash over nickel or tin/lead over nickel on soldertails. |
| 15         | 15μ" gold over nickel on mating end of contacts. Tin/lead over nickel on soldertails.              |
| 30         | 30μ" gold over nickel on mating end of contacts. Tin/lead over nickel on soldertails.              |





#### Performance Specifications (see page 4)

## D-SUBMINIATURE CONNECTORS

### K44 Series

### K44 Series Dimensions

Pictured with Board Lock Option, Dimensions in mm [In]



| Shell Size | A              | A1             | B              | C              |
|------------|----------------|----------------|----------------|----------------|
| In         | ±.010          | ±.010          | ±.005          | ±.015          |
| mm         | ±0.25          | ±0.25          | ±0.13          | ±0.38          |
| 9 (E)      | .643<br>16.33  | .666<br>16.92  | .984<br>24.99  | 1.213<br>30.81 |
| 15 (A)     | .971<br>24.66  | .994<br>25.25  | 1.312<br>33.32 | 1.541<br>39.14 |
| 25 (B)     | 1.511<br>38.38 | 1.534<br>38.96 | 1.852<br>47.04 | 2.088<br>53.04 |
| 37 (C)     | 2.159<br>54.84 | 2.182<br>55.42 | 2.500<br>63.50 | 2.729<br>69.32 |

A = Exterior of Female Shell (S)


A1 = Interior of Male Shell (P)

### Mounting Options K44, KF44


| Front Panel Mounting Options                                     | PCB Mounting Options                                                                                        |                                               |                                                                           |                                                                              |                                        |                                                                                                 |                                                                                                         |
|------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|-----------------------------------------------|---------------------------------------------------------------------------|------------------------------------------------------------------------------|----------------------------------------|-------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------|
|                                                                  | Both .125" Diameter and Oblong Non-Threaded Mounting Holes and 4-40 Hex. Jack Screws Assembled to Connector | Board Locks and .125" Diameter Mounting Holes | Top Only Grounding Straps with Non-Threaded .125" Diameter Mounting Holes | Wrap Around Grounding Straps with Non-Threaded .125" Diameter Mounting Holes | Short Mounting Flange with Board Locks | Short Mounting Flange Top Only Grounding Straps with Non-Threaded .125" Diameter Mounting Holes | Short Mounting Flange with Wrap Around Grounding Straps with Non-Threaded .125" Diameter Mounting Holes |
| Riveted Threaded Inserts                                         | <b>Not Available</b>                                                                                        | <b>P</b>                                      | <b>Q</b>                                                                  | <b>R</b>                                                                     | <b>S</b>                               | <b>M</b>                                                                                        | <b>T</b>                                                                                                |
| Riveted Threaded Inserts with 4-40 Hex. Jack Screws Installed    | <b>L*</b>                                                                                                   | <b>PJ</b>                                     | <b>QJ</b>                                                                 | <b>RJ</b>                                                                    | <b>SJ</b>                              | <b>MJ</b>                                                                                       | <b>TJ</b>                                                                                               |
| 4-40 Round Jackscrews Riveted to Connector                       | <b>Not Available</b>                                                                                        | <b>PR</b>                                     | <b>QR</b>                                                                 | <b>RR</b>                                                                    | <b>SR</b>                              | <b>MR</b>                                                                                       | <b>TR</b>                                                                                               |
| Non-Threaded Riveted Inserts                                     | <b>Not Available</b>                                                                                        | <b>PT</b>                                     | <b>QT</b>                                                                 | <b>RT</b>                                                                    | <b>ST</b>                              | <b>MT</b>                                                                                       | <b>TT</b>                                                                                               |
| Riveted Threaded Inserts with M3/4-40 Hex. Jack Screws Installed | <b>Not Available</b>                                                                                        | <b>PJM</b>                                    | <b>QJM</b>                                                                | <b>RJM</b>                                                                   | <b>SJM</b>                             | <b>MJM</b>                                                                                      | <b>TJM</b>                                                                                              |

\*Removal of jack screws will cause disassembly of L option part. Dimensions in mm [In]

### PC Board Mounting Options



### Front Panel Mounting Options



***KYCON continues its leadership in D-Subminiature connectors by offering a complete line of sizes and options.***

**PC99 Colors Available:**

- HD15: Blue
- DB15: Gold
- DB25: Burgundy
- DB09: Teal



KYCON Tech Support: **1-888-KYCON-22**  
or E-mail: [sales@kycon.com](mailto:sales@kycon.com)

## D-SUBMINIATURE CONNECTORS

### Performance Specifications

#### Materials and Finish

**Shell**

Steel Material, Tin Finish, and Indentations (Dimples) on Plug Only

**Insert**

Standard: PBT Thermoplastic, Black Color, 30% Glass Filled, 94V-0 Rated  
Reflow Compatible: High Temperature Thermoplastic, Black Color,  
30% Glass Filled, 94V-0 Rated

**Contact Material**

Pin: Brass .040 (1.02) Diameter Standard; .030 (0.76) Diameter High Density  
Socket: Phosphor Bronze (Precision Formed Contact)  
Brass (Precision Machined Contact)

**Contact Finish-Standard**

Gold Flash Over 0.0001 (0.00254) Nickel on Mating End of Contacts  
Tin/Lead Over Nickel or Gold Flash Over Nickel on Solder Tails

**Riveted Insert**

Brass Material, Nickel Finish

#### Mechanical Characteristics

**Contact Retention**

Precision Machined Contact 10 Lbs, Precision Formed Contact 10 Lbs

**Contact Extraction Force**

Typ. 4 Oz.

**Contact Insertion Force**

Typ. 9 Oz.

**Durability**

1,000 Insertion Cycles Min (With Standard Plating)

**Operating Temperature Rating**

-55°C to +125°C

#### Electrical Characteristics

**Contact Current Rating**

Precision Machined Contact 7.6 Amps  
Precision Formed Contact 5.0 Amps (Except K99 Series)

**Contact Resistance**

Precision Machined Contact 5 Milliohms Max  
Precision Formed Contact 8 Milliohms Max

**Dielectric Withstanding Voltage**

1000 V AC Min for 1 Minute

**Insulation Resistance**

5000 Megohms Min

#### Processing Characteristics

**Soldering Temperature Rating**

High Temperature Plastic: 230°C for 30 Seconds, 260°C for 10 Seconds

#### Plating Options

| Designator | Plating Description                                                                                 |
|------------|-----------------------------------------------------------------------------------------------------|
| Standard   | Gold Flash over Nickel on Contacts. Gold Flash over Nickel or Tin/Lead over Nickel on Solder Tails. |
| 15         | 15µ" Gold over Nickel on Mating End of Contacts. Tin/Lead over Nickel on Solder Tails.              |
| 30         | 30µ" Gold over Nickel on Mating End of Contacts. Tin/Lead over Nickel on Solder Tails.              |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Kycon:

[K44-A15P-MT30](#) [K44-B25S-TJ30](#) [K44-A15P-MT15](#) [K44-B25S-TT15](#) [K44-B25P-MT15](#) [K44-B25S-TT30](#) [K44-B25P-M](#) [K44-B25P-S](#) [K44-B25P-Q](#) [K44-B25P-L](#) [K44-B25P-T](#) [K44-B25P-P](#) [K44-B25P-R](#) [K44-E9P-TJ30](#) [K44-E9P-TJ15](#) [K44-A15S-PJ30](#) [K44-A15P-PR15](#) [K44-C37P-PJ15](#) [K44-B25P-SR15](#) [K44-C37P-TT30](#) [K44-E9S-P30](#) [K44-C37S-PT30](#) [K44-B25S-SJ15](#) [K44-C37P-TT15](#) [K44-B25S-SJ30](#) [K44-C37S-PT15](#) [K44-E9S-TJ](#) [K44-E9S-PT](#) [K44-E9S-TR](#) [K44-C37S-RT30](#) [K44-E9S-PJ](#) [K44-E9S-PR](#) [K44-E9S-TT](#) [K44-E9S-T15](#) [K44-C37P-SR30](#) [K44-B25S-QR](#) [K44-B25S-QT](#) [K44-B25P-QJ30](#) [K44-B25S-MJ](#) [K44-B25S-MT](#) [K44-B25S-MR](#) [K44-E9S-SR30](#) [K44-A15P-RT15](#) [K44-A15S-SR15](#) [K44-B25S-QJ](#) [K44-A15P-ST](#) [K44-A15P-SJ](#) [K44-A15P-SR](#) [K44-B25P-SR30](#) [K44-E9S-P15](#) [K44-E9P-R30](#) [K44-A15S-QR15](#) [K44-A15P-PT15](#) [K44-C37P-R30](#) [K44-E9P-R15](#) [K44-C37P-QR30](#) [K44-C37S-P30](#) [K44-B25S-R15](#) [K44-C37S-MT30](#) [K44-A15P-T15](#) [K44-C37S-MT15](#) [K44-C37P-Q15](#) [K44-C37S-S30](#) [K44-E9P-Q30](#) [K44-C37S-S15](#) [K44-C37P-Q30](#) [K44-A15S-T15](#) [K44-B25S-T30](#) [K44-B25S-T15](#) [K44-A15S-T30](#) [K44-B25P-T15](#) [K44-A15S-R15](#) [K44-B25P-T30](#) [K44-A15P-T30](#) [K44-A15S-R30](#) [K44-B25S-R30](#) [K44-C37S-TJ15](#) [K44-A15P-MJ30](#) [K44-A15P-MR30](#) [K44-A15P-MR15](#) [K44-C37S-TJ30](#) [K44-C37S-TT30](#) [K44-C37S-TT15](#) [K44-C37P-MT30](#) [K44-A15P-PJ15](#) [K44-A15P-PR30](#) [K44-A15S-PJ15](#) [K44-B25P-QT15](#) [K44-C37S-PJ30](#) [K44-A15P-PJ30](#) [K44-B25P-QT30](#) [K44-C37S-PJ15](#) [K44-E9P-SJ15](#) [K44-A15P-M30](#) [K44-E9P-SJ30](#) [K44-E9S-PT30](#) [K44-B25P-M30](#) [K44-E9S-QR15](#) [K44-B25P-M15](#) [K44-A15P-M15](#)