



P	F	LTR	DESCRIPTION	DATE	APPROVED
✓	✓	0	REC NPS 81-3231	2-28-82	TJ
✓	✓	A	ADD RG-188/U & REV STRIP LENGTH; CB3-424	7-13-83	MS/DH
✓	✓	B	ADD P/N 222000-1 PER AJ-3009	5/31/88	DBM/RJM



1. .180 MIN DIA HOLE REQ'D FOR CONTACT TO FEED THROUGH P.C. BOARD.
2. FOR USE WITH: RG-316/U, & 188/U CABLE.
3. CRIMP TOOL: 220215-2.
4. SEE IS. 2923.
7. ITEM 3 IS USED TO STABILIZE CONTACT IN THE HOUSING CAVITY; OTHERWISE DISCARD.



RECOMMENDED STRIP LENGTH

3	1	RING, ALIGNMENT	222000-1
2	1	RT. ANGLE SOCKET ASSY	228537-1
1	1	FERRULE	228538-3
ITEM	QTY	DESCRIPTION	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON:
 DECIMALS ± ____
 ANGLES ± ____

MATERIAL

FINISH

CONTRACT NO

DE T. Smith 7/25/82

CHK Michael 7/26/82

APPD Scott 7/26/82

APPD R. R. 7/26/82

DSGN APPD

OTHER APPD T. Smith 7/25/82

AMPAMP INCORPORATED
Harrisburg, Pa. 17105NAME CONNECTOR, COAXIAL, MULTIPLE, RF,
CONTACT, SOCKET, RT ANG, CA, MICROMIN

SIZE

A

FSCM NO

00779

DRAWING NO

227606-4

SCALE NTS

SHEET