



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
▶ 0,64 mm system
▶ 2 mm system
▶ 2 mm Sicherheitssystem
▶ 4 mm system
▶ 4 mm sliding sleeve system
▶ 4 mm safety system

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

sockets

sets

miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ clamp-type test probes ▶ clamp-type test probe ▶ KLEPS 2

KLEPS 2

datasheet for KLEPS 2
article number: 931467101



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 931 467-101
description:	Miniature clamp-type test probe with solder connection. Gold-plated sprung bronze contact hook for wires up to a maximum diameter of 2 mm. Remove actuator button for soldering, when cable is connected, press back on until it engages.
typ:	KLEPS 2 rot/red
system:	2mm system
order number:	931 467-101
clamping range:	max. Ø 2 mm
clamping typ:	contact hook
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	6 A
Please consider derating curve!	
contact resistance:	15 mOhm
material	
contact material:	contact hook: bronze contact spring: copper - beryllium
contact surface material:	gold
housing material:	PA
environmental conditions:	
temperature range:	-25 °C to +100 °C
inflammable class:	
housing (basic material):	UL 94 V - 2
drawing	
	