


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA07-A THRU PCA07-Z	'A' THRU 'Z'	30	300	1	10	.08" - .10"
PCA07-A-J	'A'-'J' [1 EA.]	30	300	1	10	.08" - .10"
PCA07-K-T	'K'-'T' [1 EA.]	30	300	1	10	.08" - .10"
PCA07-U-Z	'U'-'Z' [1 EA.] '-' [2 EA.] '+' [2 EA.]	30	300	1	10	.08" - .10"
PCA07-0 THRU PCA07-9	'0' THRU '9'	30	300	1	10	.08" - .10"
PCA07-0-9	'0'-'9' [1 EA.]	30	300	1	10	.08" - .10"
PCA07-MIN	'-'	30	300	1	10	.08" - .10"
PCA07-PLS	'+'	30	300	1	10	.08" - .10"

NOTES:

- COLOR: WHITE WITH BLACK LEGENDS.
- MILLIMETERS ARE IN [].



CAD FILENAME/LAYERS		100281DA-DC-C10510/04D	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING		PCA07-* CLIP-ON WIRE MARKER	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
(.X) ± .062 (.XXX) ± .015		(.XX) ± .031 ANGLES ±	
DRAWN BY RVU		MAT'L:	
DATE 9-16-96		WHITE MARKER - ACETAL	
CHK'D		SCALE	
REV		DRAWING NO. C10510	
DATE		DWG SIZE A	
BY			
CHK			

4	3/28/11	RVU	ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [1 EA.].	6336	R				
3	8/11/10	RVU	UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079	R				
2	2-15-07	RVU	ADD TOL. AND NOTES 1 THRU 5. ADD P/N.	4882	R				
1	10-06-06	RVU	REMOVED "PMW" ON ALL PART NUMBERS.	4716	R				
0	9-12-06	RVU	DRAWING RELEASE	4677	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCA07-1](#) [PCA07-2](#) [PCA07-3](#) [PCA07-4](#) [PCA07-5](#) [PCA07-6](#) [PCA07-7](#) [PCA07-8](#) [PCA07-A](#) [PCA07-PLS](#) [PCA07-S](#)
[PCA07-B](#) [PCA07-J](#) [PCA07-L](#) [PCA07-O](#) [PCA07-E](#) [PCA07-C](#) [PCA07-W](#) [PCA07-H](#) [PCA07-T](#) [PCA07-Z](#) [PCA07-A-](#)
[J](#) [PCA07-K-T](#) [PCA07-G](#) [PCA07-MIN](#) [PCA07-N](#) [PCA07-M](#) [PCA07-K](#) [PCA07-X](#) [PCA07-U-Z](#) [PCA07-Y](#) [PCA07-I](#)
[PCA07-V](#) [PCA07-F](#) [PCA07-D](#) [PCA07-Q](#) [PCA07-U](#) [PCA07-P](#) [PCA07-R](#)