


GB




General purpose floodlight that features a high impact anticorrosive polycarbonate lens and body. Integral control gear and also available complete with lamp which makes this floodlight speedy and simple to install. Standard body colours are Black, White or Silver Grey. Suitable for all types of applications and weather conditions. For dusk to dawn operation photocell versions are available for all types.





-  S.1 - SON-E  (E27) Internal ignitor
-  H.1 - Metal Halide (RX7s)
-  H.3 - Metal Halide (E27)
-  CF.4 - Compact fluorescent, 2 pin, (GX24d-3) - triple
-  CF.5 - Compact fluorescent, 4 pin, (GX24d-4) - triple
-  M.1 - MBF/U (E27)



DESCRIPTION	LAMP	Wt.(kg)	PART No.	WHITE	SILVER
SYMMETRIC REFLECTOR POLYCARBONATE IP65					
HIGH PRESSURE SODIUM 					
70W - BLACK	S.1	3.90	GB70S	/W	/S
METAL HALIDE					
70W - BLACK	H.1	3.90	GB70H	/W	/S
100W - BLACK E27	H.3	3.90	GB100H	/W	/S
COMPACT FLUORESCENT					
26W - BLACK	CF.4	3.90	GB26	/W	/S
32W - BLACK	CF.5	3.90	GB32	/W	/S
2 X 26W* HF	CF.5	3.90	GB52	/W	/S
2 X 32W* HF	CF.5	3.90	GB64	/W	/S
MERCURY					
80W - BLACK	M.1	3.90	GB80M	/W	/S
*Twin HF Ballast Unit					

 PHOTOCELL OPTIONS ARE AVAILABLE ON ALL TYPES, TO ORDER SUFFIX CODE WITH /PC. e.g. GB70S/PC

TECHNICAL SPECIFICATION

HOUSING & FRAME	Thermo-plastic polycarbonate
DIFFUSERS	Polycarbonate
PHOTOCELL	Photocell available for all types
REFLECTORS	Anodised polished aluminium
CONTROL GEAR	Available with a wide variety of options
SUPPLY ACCESS	Hinged front cover opening
COLOURS	Black RAL 9011, Silver RAL 7000, White RAL 9003

WINDAGE SCX=0.11M2

