




Dimensions: mm (in.)

**P.C. Mounting**

POS.1	POS.2
ON	ON
2-3	2-1

Switch Function**Electrical Specifications:**

- Contact resistance: 20mΩ max. initial @ 2-4VDC 100mA
- Insulation resistance: 1,000MΩ min.
- Dielectric strength: 1,000 V RMS@sea level
- Rating: 0.4 Volt-Amps (VA) max. / 20V max. (AC or DC)

Mechanical Specifications:

- Mechanical life: 50,000 make-and-break cycles
- Operating temperature: -30°C to 85°C

Soldering Process:

- Wave Soldering: Recommended soldering temperature: 260±5°C
Duration of solder immersion: 5±1 sec.
(PCB is 1.6mm in thickness)

Note:

- RoHS Compliant by Exemption

Sealed Sub-Miniature Toggle Switch (SMT)
108-2BS1T1T45-EVX

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2BS1T1T45-EVX](#)