

TR14D3E Product Details



TR14D3E (1-1423393-6)

TE Internal Number: 1-1423393-6

 Preliminary

 [Add to Part List](#)

Time Delay Relays

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- TR Series
- Control Relay - Timing Version
- Input Voltage = 215 VDC
- Contact Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact Rating = 10A

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Wiring Diagram](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Control Relay - Timing Version
- Termination Type = 16 Flat Base Pins
- Magnetic Blow-Out Device = Without

Electrical Characteristics:

- Input Voltage (VDC) = 215
- Contact Rating = 10A

Body Related Features:

- Series = TR

Contact Related Features:

- Mounting Options = Socket
- Mode of Operation = Delay on Energization
- Delay Time = 4 seconds to 120 seconds
- Type of Control = Potentiometer Adjustable
- Repeatability, Max. = $\pm 2\%$
- Approved Standards = CSA Certified, UL Listed
- Contact Material = Silver Plated
- Approx. Dimensions (L x W x H) (mm [in]) = 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]

Configuration Related Features:

- [Contact Arrangement](#) = 4 Form C, 4PDT, 4 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Conditions for Usage:

- Temperature Range (°C) = 0 – 50

Other:

- Brand = Agastat