




► ISO 5749, DIN ISO 5749, NF E 73-105

- Edges designed for clean cut in copper wire.
- High-frequency hardened cutting edges for durable cut accuracy.
- Snipe nose for manoeuvrability in control cabinets or cutting cable loom ties.
- 4 options
- CPE Chrome finish, ergonomic grips, return spring.
- TE Varnish finish, ergonomic grips, return spring.
- G Varnish finish, PVC grips.
- VE Varnish finish, return spring, 1000V insulated grips for electrical safety to EN 60900 and , for working on or near live components.



▼ Données Techniques

	 max mm Cu	B1 mm	B2 mm	L mm	A mm	C mm	 g
391.16CPE	3,5	21	13,5	165	19	10	190
391.16TE	3,5	21	13,5	165	19	10	190
391.16G	3,5	21	13,5	160	19	10	160
391.16VE	3,5	21	13,5	165	19	10	200