



product details

KIT LED PRO CARRÉ 1x5 W



Product description: KIT LED PRO CARRÉ 1x5 W
EAN/ Product: 4008321399021
Quantity: Folding carton box (FS) contains 1 Piece (PCE)

You can find this product in the eCatalog:
http://catalog.myosram.com?~language=EN&~country=COM&it_p=4008321399021

Applications	
Holder designation	GU10
Protection class IK (shock resistance)	IK02
Protection class	II
Adjustable	Yes
Type of connection	FIXED CONNECTION (TERMINAL)
IP code	IP23
Protection against ignition and fire	F
General Description	
Equipment	UNKNOWN
Body material	ALU-DIECAST
Recycling	Yes
Number of lighting outlets	1
Equipped with lamp	Yes
Standards	CE
Technical - Colors	
Color of the luminaire	BRUSHED NICKEL
Technical - Electrical Data	
Nominal current	22.00 M A
Operating mode	NOT RELEVANT
Nominal wattage	5 W
Nominal voltage	230 V
Mains frequency	50-60 Hz
Technical - Geometries	
Length	90 mm
Mounting diameter	80 mm
Width	90 mm
Mounting depth	≥ 150 mm
Height	90 mm
Technical - Light Technical Data	
Color temperature	3000 K
Beam angle	20 °
Luminous intensity	375 cd
Technical - Temperatures	
Glow Wire Test according to IEC 695-2-1	960 °C



product details

KIT LED PRO CARRÉ 1x5 W

Packaging units				
EAN	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4008321399021	Folding carton box contains 1 Piece	114,000 mm x 112,000 mm x 145,000 mm	264,890 g (260,000 g)	1,851 Cubic dec.
4008321399038	Shipping carton box contains 6 Piece	139,000 mm x 242,000 mm x 307,000 mm	1,884 kg (1,560 kg)	10,327 Cubic dec.

KIT LED PRO

KIT LED PRO is a set that is ready for installation and consists of a downlight with connecting terminal and a PARATHOM PAR 16 LED in two different versions (square/round). It is ideal for constant economical lighting in retail outlets, hotels and restaurants.

- Die-cast aluminum casing in two versions: square and round
- Luminaire color: brushed nickel look
- Simple installation and maintenance thanks to the Twist&Lock interlock for the lamp
- Lamp swivels through 40°
- Operating temperature 15 °C to +40 °C
- Mounting diameter 80 mm
- Direct connection to 230 V
- Equipped with PARATHOM PAR 16 4.5 W LED
- Average life 35,000 hours
- Color temperature warm white (3000 K)
- Beam angle 30°
- Not dimmable
- CE Sign Protection class 2 sign F Sign IP 23, Glow wire test at 850 °C, IK02, Light color 830, 220-240 V, 50-60 Hz, GU10 base