




Isolierkörpermaterial

Nylon, UL94V-0

Kontaktmaterial

Phosphorbronze

Kontaktoberfläche

Ni, Au / Sn

Kontaktwiderstand

30mΩ max

Isolationswiderstand

1000MΩ min

Strombelastbarkeit

1.5A

Betriebstemperatur

-40°C - +85°C

Betriebsspannung

125V AC

Prüfspannung

1000V AC

Verpackung

Blisterverpackung

Insulator material

Nylon, UL94V-0

Contact material

Phosphor bronze

Plating

Ni, Au / Sn

Contact resistance

40mΩ max

Insulation resistance

1000MΩ min

Current rating

1.5A

Operating temperature

-40°C - +85°C

Operating voltage

125V DC


Test voltage

1000V AC



Packing

Tray packing

Dimensions			
No. of contacts	A	B	C
4 (RJ10)	11.43	3.81	7.62
6 (RJ12)	13.46	6.35	10.16
8 (RJ45)	15.20	8.89	11.43



PC Board Layout
Component Side Shown



Bestellcode / Ordercode

Polzahl

- 0 - 4 polig (RJ10)
- 1 - 6 polig (RJ12)
- 2 - 8 polig (RJ45)

No. of contacts

- 0 - 4 contacts (RJ10)
- 1 - 6 contacts (RJ12)
- 2 - 8 contacts (RJ45)

A - 2014 x

Bitte „x“ durch die geeignete Option ersetzen
Please replace „x“ with appropriate option