


AMP WIRE RANGE	 E13288 Listed	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED



- 1 FOR $\varnothing 3.810[\varnothing.150]$ TO $\varnothing 5.842[\varnothing.230]$ WIRE INSULATION.
- 2 BODY MATERIAL THK: $1.016\pm 0.051[.040\pm.002]$
- 3

APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 4

STAMP AMP 12-10* APPROX AS SHOWN.
- 5

MATERIAL:
BODY & SLEEVE: COPPER PER (ASTM-B152)
INSULATION: NYLON.
- 6


FINISH:
BODY & SLEEVE: TIN PLATED PER (ASTM-B545)
INSULATION: COLOR-YELLOW.

500	LOOSE PIECE	324915
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F] MAX VOLTAGE RATING: 300 V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE, 2.62-6.64mm²[5,180-13,100] SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .127[.005] 4 PLC ± - ANGLES ± 5° FINISH
MATERIAL 5	6

DWN RAGHAVENDRA 27AUG09	 TE Connectivity				
CHK JEFF RUTH 27AUG09					
APVD TOM MICHIELUTTI 27AUG09					
PRODUCT SPEC					
APPLICATION SPEC 114-2157	NAME WIRE TERMINAL PIDG - RING TONGUE WIRE SIZE: 12-10 AWG				
WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C=324915	RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 6:1	SHEET 1 OF 1	REV G2